

Convert 60mm M.2 NGFF SATA SSD to 1.8" SATA Drive

1. Introduction

Best Solution that Convert Fast Speed M.2 NGFF 6Gbps SATA based SSD to Standard 3.3V 1.8-inch 16Pin SATA Solid State Drive!

1.1. Features

- Convert 3.3V M.2 NGFF SATA based SSD to standard 3.3V 1.8" SATA drive Form Factor
- Supports 6Gbps, 3Gbps SATA based M.2 NGFF 60mm, 42mm, 30mm SSD
- M.2 NGFF type 2260-D5-B connector on board
- Movable M.2 NGFF stand-off and multiple plated-holes supports type 2260, 2242 and 2230 SSD
- Supports dual-sided SSD module 1.5mm component height on the top and bottom side
- 16Pin micro SATA (Signals and Power) male connector on board
- M.2 NGFF SATA SSD can be the primary bootable device containing the OS and application.
- Operating system independent and no driver required
- Supports any OS like Windows, Mac and Linux
- Supports industrial operating temperature range: -40 - 85 °C
- Fully RoHS compliant

2. Installation

1. Plug 60mm or 42mm or 30mm M.2 NGFF SATA SSD module into M.2 NGFF socket on board, push the other end of NGFF SSD module down and screw to PCB.
2. Install Converter Adapter with NGFF SSD into 1.8" drive bay.
3. Connect SATA Signals & Power to 16Pin connector.