

Red Line Lasermodule

LI635-5-3(8x26)-F250

Order Number: 70116717

Main Parameters (*)	min	typ	max	Unit
Wavelength		635		nm
Optical Output Power		5		mW
Operating Voltage	2.7	3	3.3	V DC
Operating Current	35	52	70	mA
Operating Temperature	-20		50	°C
Storage Temperature	-40		80	°C

Optical Parameters

Beam Shape	Line
Laser Class	1
Divergence	1.5mrad
Fan Angle	90°
Line Thickness	<0.3mm@0.25m
Operating Distance	0.25m
Optics	glass lens AR coated
Laser technology	Single Mode Diode
Focus	fixed (250mm)

Technical Parameters

Lifetime	>10000h
RoHS	yes

Electrical Parameters

Potential of Housing	isolated
Power Supply	LFNT-3

Mechanical Parameters

Size	Ø8x26mm
Material	aluminium
Cable length	100mm
Wire type	26AWG, 0,14mm ²
Output Aperture	3mm
Housing Color	black
Weight	4g
Stripping of wire	5mm

(*) Over the complete operating temperature range

Features





- Laser Class 1
- Low power consumption
- For medical devices
- Uniform line thickness
- Image processing


Picture




Cable Colors

Ground		blue	GND
Positive		red	2.7 - 3.3, typ 3V DC

Drawing



Safety Label



Revision

REV 23 | 11-JUL-2014