



VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

"Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success."

VC-519 CLAMP MULTIMETER



VERSION 12/21

Nº 1386328

Compact AC current clamp with multimeter functions. The clamp multimeter enables non-contact AC current measurements without interrupting the circuit. A built-in torch allows measuring point illumination in low light conditions. Despite its small size, a good one-handed operation is possible even when wearing protective gloves.

FEATURES:

CAT III 600 V // Integrated LED torch //

EQUIPMENT:

Measuring functions: DC/AC current // alternating current // resistance // temperature // diode test // audible continuity tester // automatic shutdown // battery change indicator // non-contact AC voltage detection // automatic/manual range selection // selectable display backlight // hold function //

TECHNICAL DATA:

Display:	2000 counts
Measuring type:	arithmetic mean
Voltage measurement:	AC/DC
Measuring range V/DC:	0.1 mV - 600 V
Measuring range V/AC:	0.1 mV - 600 V
Basic accuracy:	±1.5 %
Frequency range:	50 - 60 Hz
DC/AC internal resistance:	10 MΩ
Current measurement:	AC
Measurement range A/AC:	0.01 - 400 A
Measurement range resistance:	0.1 Ω - 20 MΩ
Measurement range temperature:	-20 to +760 °C
Opening range for current clamp:	30 mm
Measurement category:	CAT III 600 V
Power supply:	2x 1.5 V micro batteries (AAA, LR3)
Automatic shut-down:	after ca. 15 minutes, cannot be deactivated
Product dimensions (L x W x H):	200 x 70 x 38 mm
Weight:	230 g



PACKAGE CONTENTS:

Digital clamp multimeter // 2 x safety test leads with removable CAT III covers // Plug adapter thermocouple - banana plug // Wire temperature probe (-40 to +230 °C, type K thermocouple plug) // 2 x AAA batteries // Bag // Operating instructions //

Legal notice

This data sheet is published by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data sheet represent the technical status at the time of printing.

© Copyright 2022 by Conrad Electronic SE

1386328_V2_1221_01_PIX_ds