


Dept  
Qty  
DC 1  
ED 1  
IE 1  
ISO 1  
PD 1  
R&D 1  
SD 1  
QA 1  
QC 1  
QE 1

The information provided herein is from CONNELY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNELY or its affiliates. Unauthorized use or reproduction of this document in any form or by any means, electronic or mechanical, including photocopying, recording, or by any information storage and retrieval system, without prior written permission from CONNELY is strictly prohibited. CONNELY may enforce its intellectual property rights at its own discretion, failures or delays to exercise such rights does not constitute a waiver of such rights.



(Series Image-Reference Only)

|                   |       |                  |       |            |                                                                                                                                                  |        |                                                 |  |
|-------------------|-------|------------------|-------|------------|--------------------------------------------------------------------------------------------------------------------------------------------------|--------|-------------------------------------------------|--|
| GENERAL TOLERANCE |       | ANGLE TOLERANCE  |       | PROJECTION |                                                             | TITLE  | IDC SOCKET PITCH 2.0mm<br>WITH 1.0mm FLAT CABLE |  |
| X.                | ±0.60 | X.               | ±5°   | UNITS      | mm                                                                                                                                               |        |                                                 |  |
| .X                | ±0.38 | .X               | ±3°   | SHEET SIZE | A4                                                                                                                                               | SERIES | DS1017 SERIES                                   |  |
| .XX               | ±0.25 | .XX              | ±2°   |            |                                                                                                                                                  |        |                                                 |  |
| DRAWING TYPE      |       | CUSTOMER         |       |            |  <div>晨翔电子有限公司<br/>CONNFLY CONNELY ELECTRONIC CO. LTD</div> |        |                                                 |  |
| SCALE             |       | 1:1              | SHEET | 1 OF 1     |                                                                                                                                                  |        |                                                 |  |
| DRAWING NO.       |       | C-DS1017-XXXXX-D |       |            |                                                                                                                                                  |        |                                                 |  |

| REV. | DESCRIPTION    | DRAWN         | CHECKED       | APPROVED      |
|------|----------------|---------------|---------------|---------------|
| A    | NEW RELEASE    | LJH 04/27/05' |               | LJC 04/27/05' |
| B    | DRAWING UPDATE | YCH 07/27/11' |               | LJC 07/27/11' |
| C    | ADD P/N CODE   | JLZ 01/06/15' | HZW 01/06/15' | LJC 01/06/15' |
| D    | DRAWING UPDATE | JLZ 08/28/18' |               |               |

NOTES:

1. Materials
- 1.1 Insulator:Thermoplastic(UL 94V-0).
- 1.2 Contact:Copper alloy.
2. Specification
- 2.1 Temperature range:-40--+105°C.
- 2.2 Contact resistance:20mΩ max.
- 2.3 Insulation resistance:1000MΩ min.
- 2.4 Dielectric withstanding voltage:AC 500V per minute.
3. Part number code:
- DS1017- X X X X X
- Housing color  
G: Gray  
B: Black  
L: Blue
- Contact plating  
8: Full gold flash  
6: Full tin  
2: Nickel+Gold flash
- Polarization  
A: W/  
B: W/O
- Strain relief  
M: W/  
N: W/O
- No. of contacts  
10 12 14 16 20 22 24 26  
30 34 36 40 44 50 56 64



晨翔电子有限公司  
CONNFLY CONNELY ELECTRONIC CO. LTD