



Nominal Voltage:	3.0 V
Typical Voltage:	3.2-3.3 V
Nominal Internal Impedance:	0.25 ohm @ 1kHz
Average Weight:	17.0 gm
Volume:	7.18 cm ³
Terminals:	Flat, Recessed Negative Terminal, Nickel Plated Steel
Operating Temperature Range:	-20°C to 60°C (-4°F to 140°F)
ANSI:	5018LC
IEC:	CR17345

**Delivered Energy vs. Power Drain
@ Various Cutoff Voltage - Room Temperature**




Duracell Ultra 123 Typical Performance




* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.


1.8 Amp 3 sec on / 7 sec off
 @ Various Temperatures




1.2 Amp, 3 sec on / 7 sec off
 @ Various Temperatures



Continuous Discharge
 RT to 1.7 Volts



0.9 Amp, 3 sec on / 27 sec off
 @ Various Temperatures



DURACELL[®]
 BATTERIES

Berkshire Corporate Park
 Bethel, CT 06801 U.S.A.
 Telephone: Toll-free 1-800-544-5454
 Internet: www.duracell.com

* Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.