







Features

- Universal AC input / Full range (up to 305VAC)
- · Built-in active PFC function
- No load power consumption <0.5W at remote OFF
- High efficiency up to 96%
- -40 $^\circ \rm C$ ~ +70 $^\circ \rm C$ wide operating range
- Protections: Short circuit / Over current / Over voltage
 / Over temperature
- · Fanless design, cooling by free air convection
- · IP67 / IP65 design for indoor or outdoor installations
- Withstand 5G vibration test
- Three in one dimming function (0~10Vdc or PWM signal or resistance)
- · Suitable for dry / damp / wet location
- 5 years warranty (Note.10)

Description

HLG-600H series is a high performance dustproof and waterproof AC-to-DC LED power supply up to 600Watts. The fully-potted silicone and the aluminum case facilitate the heat dissipation. Above all, it delivers the efficiency up to 96% that tops the LED power supply field. Other features include the wide working temperature range between -40° C and $+70^{\circ}$ C, the fan-less design, the adjustable output voltage and current, the surge susceptibility up to 4KV (EN61000-4-5), low no-load power consumption (<0.5Watt) at remote OFF and workable for 277VAC input. These attributes all make HLG-600H the fit for the indoor/outdoor LED lighting application requiring remarkable reliability.

Model Encoding HLG - 600H - 12 A Function mode option Function mode option Output voltage High input voltage up to 305VAC Output power Series name A : IP65, Vo and Io level can be adjusted through internal potentiometer. B : IP67, Io adjustable with 0~10Vdc, PWM signal or resistance.

Applications


- LED street lighting
- LED high-bay lighting
- · Parking space lighting
- · LED searchlight
- LED fishing lamp



SPECIFICATION

MODEL			HLG-600H-12	HLG-600H-15	HLG-600H-20	HLG-600H-24	HLG-600H-30	HLG-600H-36	HLG-600H-42	HLG-600H-48	HLG-600H-54			
	DC VOLTAGE		12V	15V	20V	24V	30V	36V	42V	48V	54V			
	CONSTANT CURRENT	REGION Note 4		7.5 ~ 15V	10~20V	12~24V	15~30V	18 ~ 36V	21~42V	24~48V	27 ~ 54V			
	RATED CURRENT		40A	36A	28A	25A	20A	16.7A	14.3A	12.5A	11.2A			
	RATED POWER		480W	540W	560W	600W	600W	601.2W	600.6W	600W	604.8W			
	RIPPLE & NOISE ((max) Note 2		150mVp-p	150mVp-p	150mVp-p	200mVp-p	250mVp-p	250mVp-p	250mVp-p	350mVp-p			
	VOLTAGE ADJ. RANGE Note.6						25.5 ~ 31.5V							
OUTPUT				ed by internal p			20.0 01.01	0010 01101		10.0 00.11	10.0 00.11			
	CURRENT ADJ. RANGE		20~40A	18 ~ 36A	14 ~ 28A	12.5 ~ 25A	10~20A	8.3~16.7A	7.1~14.3A	6.2 ~ 12.5A	5.6 ~ 11.2A			
	VOLTAGE TOLERANCE Note.3			±2.0%	±1.5%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%			
	LINE REGULATION		±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%			
	LOAD REGULATION		±2.0%	±1.5%	±1.0%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	$\pm 0.5\%$			
	SETUP, RISE TIMI	-	500ms, 80ms		30VAC /115VA			_ 010 /0		_0.070	_0.070			
	HOLD UP TIME (Typ.)		15ms at full lo			0								
	VOLTAGE RANGE		90 ~ 305VAC	127 ~ 431										
	FREQUENCY RAN		47 ~ 63Hz	127 401	VDO									
	POWER FACTOR (Typ.)			AC PE>0 95/2	301/AC PE>0	03/277\/AC at	full load (Pleas	a rafar to "Pow	er Factor Char	actoristic" curv	<i>م</i>)			
	TOTAL HARMONIC DISTORTION		PF>0.98/115VAC, PF>0.95/230VAC, PF>0.93/277VAC at full load (Please refer to "Power Factor Characteristic" curve) THD< 20% when output loading ≥50% at 115VAC/230VAC input and output loading ≥75% at 277VAC input											
	EFFICIENCY	230VAC	92%	93.5%	94.5%	95%	95%	95.5%	96%	96%	96%			
INPUT	(Typ.)	277VAC	92.5%	93.5%	94.5%	95%	95%	95.5%	96%	96%	96%			
	AC CURRENT (Ty		7A / 115VAC				5570	33.370	5070	5070	5070			
	INRUSH CURRENT(Typ.)		7A / 115VAC 3.3A / 230VAC 2.9A / 277VAC COLD START 70A(twidth=1000);/s measured at 50% peak) at 230VAC 200VAC											
	LEAKAGE CURRENT		COLD START POA(twidth-1000)25 Theasured at 50 % (peak) at 250 VAC < 0.75mA / 277VAC											
		_141	95~108%											
	OVER CURRENT	Note.4		a . Canadant a	une of limiting		a ati a a llu a afta a fu							
			Protection type : Constant current limiting, recovers automatically after fault condition is removed											
PROTECTION	SHORT CIRCUIT OVER VOLTAGE		Constant current limiting, recovers automatically after fault condition is removed 13 ~ 16V 16.5 ~ 20.5V 22 ~ 26V 26 ~ 30V 32.5 ~ 36.5V 39.5 ~ 43.5V 46 ~ 50V 52.5 ~ 56.5V 59 ~ 63V											
			Protection type : Shut down o/p voltage, re-power on to recover											
			Shut down o/p voltage, re-power on to recover											
	OVER TEMPERAT													
FUNCTION	REMOTE ON/OFF CONTROL		$5V_{SB}: 5V@0.5A; tolerance \pm 5\%, ripple : 100mVp-p(max.)$											
	5V STANDBY		$-40 \sim +70^{\circ}C$ (Refer to "Derating Curve")											
	WORKING TEMP.		20 ~ 95% RH non-condensing											
	WORKING HUMIDITY													
ENVIRONMENT	STORAGE TEMP., HUMIDITY		±0.03%/℃ (0~60℃)											
	TEMP. COEFFICIENT													
	VIBRATION		10 ~ 500Hz, 5G 12min./1cycle, period for 72min. each along X, Y, Z axes											
	SAFETY STANDA													
SAFETY &	WITHSTAND VOL	-	I/P-O/P:3.75KVAC I/P-FG:2KVAC O/P-FG:0.5KVAC											
EMC	ISOLATION RESIS	DIANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH											
	EMC EMISSION		Compliance to EN55015, EN55022(CISPR22) Class B, EN61000-3-2 Class C (≧50% load) ; EN61000-3-3											
	EMC IMMUNITY		Compliance to EN61000-4-2,3,4,5,6,8,11, EN61547, EN55024, light industry level (surge 4KV), criteria A											
OTUEDO	MTBF		76.9K hrs min. MIL-HDBK-217F (25°C)											
OTHERS	DIMENSION		280*144*48.5mm (L*W*H) 3.9Kq; 4pcs/16.6Kq/0.9CUFT											
	PACKING	NOT	0, 1	0			and of °C (
NOTE	 All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. Tolerance : includes set up tolerance, line regulation and load regulation. Constant current operation region is within 50%-100% rated output voltage. This is the suitable operation region for LED related applications, but please reconfirm special electrical requirements for some specific system design. Derating may be needed under low input voltages. Please check the static characteristics for more details. A type only. Safety and EMC design refer to EN60598-1, subject CNS15233, GB7000.1, FCC part18. Length of set up time is measured at cold first start. Turning ON/OFF the power supply may lead to increase of the set up time. The power supply is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by t complete installation, the final equipment manufacturers must re-quality EMC Directive on the complete installation again. 													








EFFICIENCY vs LOAD (54V Model)

HLG-600H series possess superior working efficiency that up to 96% can be reached in field applications.




DRIVING METHODS OF LED MODULE

There are two major kinds of LED drive method "direct drive" and "with LED driver".

A typical LED power supply may either work in "constant voltage mode (CV) or constant current mode (CC)" to drive the LEDs.

Mean Well's LED power supply with CV+ CC characteristic can be operated at both CV mode (with LED driver, at area (A) and CC mode (direct drive, at area (B).




Typical LED power supply I-V curve

In the constant current region, the highest voltage at the output of the driver depends on the configuration of the end systems.

Should there be any compatibility issues, please contact MEAN WELL.





% Built-in 3 in 1 dimming function, IP67 rated. Output constant current level can be adjusted through output cable by connecting a resistance or 0 ~ 10Vdc or 10V PWM signal between DIM+ and DIM-.

※ Please DO NOT connect "DIM-" to "-V".

 $\% \, {\rm Reference} \, {\rm resistance} \, {\rm value} \, {\rm for} \, {\rm output} \, {\rm current} \, {\rm adjustment} \, ({\rm Typical})$

Resistance value	Single driver	Short	10K Ω	20K Ω	30K Ω	40K Ω	50Κ Ω	60K Ω	70K Ω	80K Ω	90Κ Ω	100K Ω	OPEN
	Multiple drivers (N=d river quantity for synchronized dimming operation)	Short	10KΩ/N	20KΩ/N	30K Ω <i>I</i> N	40K Ω /N	50K Ω /N	60KΩ/N	70KΩ/N	80KΩ/N	90KΩ/N	100KΩ/N	
Percentage	e of rated current	0%	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	95%~108%

% 0 ~ 10V dimming function for output current adjustment (Typical)

Dimming value	0 V	1V	2V	3V	4V	5V	6V	7V	8V	9V	10 V	OPEN
Percentage of rated current	0%	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	95%~108%

% 10V PWM signal for output current adjustment (Typical): Frequency range :100Hz ~ 3KHz

Dutyvalue	0%	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	OPEN
Percentage of rated current	0%	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	95%~108%

%Direct connecting to LEDs is suggested, but is not suitable for using additional drivers.



