



8. Suitable for BF application with appropriate system consideration.

■ Features :

- Universal AC input / Full range
- Low leakage current <100µA
- Protections: Short circuit / Overload / Over voltage
- Free air convection for rated power and 23.5CFM forced air convection for peak load
- Medical safety approved (2 x MOPP between primary to secondary)(Note.8)
- No load power consumption<0.75W
- Fixed switching frequency at 65KHz
- 3 years warranty

CBCE

SPECIFICATION MODEL RPS-75-3.3 RPS-75-5 RPS-75-12 RPS-75-15 RPS-75-24 RPS-75-36 RPS-75-48 DC VOLTAGE 3.3V 5V 12V 15V 24V 36V 48V RATED CURRENT 15A 14A 6.3A 5A 3.2A 2.1A 1.6A **CURRENT RANGE** 0 ~ 20A 0~18.7A 0~8.3A 0~6.7A 0~4.2A 0 ~ 2.8A 0 ~ 2.1A RATED POWER 49.5W 70W 75 6W 75W 76.8W 75.6W 76.8W PEAK LOAD (23.5CFM) 66W 93.5W 99.6W 100.5W 100.8W 100.8W 100.8W RIPPLE & NOISE (max.) Note 2 80m Vp-p 80mVp-p 120mVp-p 150mVp-p 240mVp-p 300mVp-p 300mVp-p **OUTPUT** VOLTAGE ADJ. RANGE $29 \sim 36V$ 4.75 ~ 5.5V 11.4 ~ 13.2V 13.5 ~ 16.5V 22.8 ~ 27.6V 34.2 ~ 39.6V 45.6 ~ 52.8V VOLTAGE TOLERANCE Note.3 ±2.0% ±2.0% ±1.0% ±1.0% ±1.0% ±1.0% ±1.0% LINE REGULATION ±0.5% ±0.5% ±0.5% ±0.5% ±0.5% ±0.5% ±0.5% LOAD REGULATION +1.5% ±1.5% ±1.0% +1.0% ±1.0% ±1.0% ±1.0% SETUP, RISE TIME 500 ms, 30 ms/230 VAC 500ms, 30ms/115VAC at full load HOLD UP TIME (Typ.) 80ms/230VAC 20ms/115VAC at full load 90 ~ 264VAC **VOLTAGE RANGE** 127~370VDC FREQUENCY RANGE 47 ~ 63Hz 73% 82% 83% 85% 86% 86% EFFICIENCY(Typ.) 78% INPUT AC CURRENT (Typ.) 1.5A/115VAC 1A/230VAC INRUSH CURRENT (Typ.) COLD START 25A/115VAC 50A/230VAC LEAKAGE CURRENT Note.7 Earth leakage current < 150μ A/264VAC , Touch current < 100μ A/264VAC 140 ~ 180% rated output power **OVERLOAD** Protection type: Hiccup mode, recovers automatically after fault condition is removed. PROTECTION 17.25 ~ 20.25V 27.6 ~ 32.4V 3.8 ~ 4.46V 5.75 ~ 6.75V 13.8 ~ 16.2V 41.4 ~ 48.6V 55.2 ~ 64.8V **OVER VOLTAGE** Protection type: Shut down o/p voltage, re-power to recover WORKING TEMP. -20 ~ +70°C (Refer to "Derating Curve") 20 ~ 90% RH non-condensing **WORKING HUMIDITY** ENVIRONMENT STORAGE TEMP., HUMIDITY -40 ~ +85°C, 10 ~ 95% RH TEMP. COEFFICIENT ±0.03%/°C (0 ~ 45°C) VIBRATION 10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes **SAFETY STANDARDS** ANSI/AAMI ES60601-1, TUV EN60601-1, IEC60601-1 approved WITHSTAND VOLTAGE I/P-O/P:4KVAC I/P-FG:2KVAC O/P-FG:1.5KVAC SAFETY & I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH ISOLATION RESISTANCE EMC (Note 4) **EMC EMISSION** Compliance to EN55011 (CISPR11), EN55022 (CISPR22) Class B, EN61000-3-2,-3 **EMC IMMUNITY** Compliance to EN61000-4-2,3,4,5,6,8,11, EN55024, EN60601-1-2, EN61000-6-2, EN61204-3, heavy industry level, EN61204-3 medical level, criteria A **MTBF** 446.8K hrs min. MIL-HDBK-217F (25°C) **OTHERS** DIMENSION 127*76.2*31mm (L*W*H) PACKING 0.26Kg; 63pcs/16.3Kg/1.35CUFT 1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25℃ of ambient temperature. NOTE 2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. 3. Tolerance: includes set up tolerance, line regulation and load regulation. 4. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on http://www.meanwell.com) 5. Length of set up time is measured at cold first start. Turning ON/OFF the power supply may lead to increase of the set up time. 6. Heat Sink HS1, HS2, HS3 can not be shorted. 7. Touch current was measured from primary input to DC output.



