



	Bestell No.	UNO ITEM NO.	LENGTH
	1404164	744111.50	500+100/-0
	1404165	744111.11	1000+100/-0
	1404166	744111.81	1800+100/-0
	1404167	744111.05	5000+100/-0
	1404168	744111.07	7500+100/-0
	1404169	744111.00	10000+100/-0
	1404170	744111.20	20000+100/-0

PIN OUT

VGA(HD15)M	VGA(HD15)M
1 RED	1
6 DRAIN	6
2 BLUE	2
7 DRAIN	7
3 GREEN	3
8 DRAIN	8
4 GREEN	4
5 GRAY	5
9	9
10 PURPLE	10
11 RED	11
12 RED	12
13 TRANSPARENT	13
14 ORANGE	14
15 WHITE	15
SHEEL BRAID+DRAIN SHEEL	

NOTE:

- Electrical test:
  - 100% open short & miss wire test;
  - Insulation resistance:DC 300V 10Mohm;
  - Contact resistance:3ohm Max;
  - Dielectric strength:100V AC/Minute, 1mA.
- Computer practical application Test Pass (800\*600)
- Operation temperature:-10°C ~ +60°C  
Storage temperature:-20°C ~ +75°C  
Operation humidity:10%~85%  
Storage humidity:10%~85%  
weight of unit (w/o packing): 29212c38/165.5g
- PRINTING:AWM 2919 80°C 30V VW-1 VGA CABLE
- PACKING:1PCS/Renkforce giftbox
- ROSH2.0 AND REACH COMPLIANT

MATERIAL LIST:

NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK
⑥	FERRITE CORE	ID:9.5*OD:17.5*28.5MM , OUTER MOLD PVC BLACK	2	
⑤	MOLDED THUMB SCREW	Nickel Flash #4-40 MOLDER BLACK	4	
④	INNER MOLD	LD-PE	2	
③	OUTER MOLD	PVC COLOR BLACK	2	
②	CABLE	(28AWG BC+S+PVC)*3+28AWG BC*7C+AEB PVC/BLACK OD:7.0±0.2mm	1	
①	VGA CONNECTOR	VGA 15P/M Solder Type, blue PBT insulation, The Pin Gold Plating, The shell Nickel Plating	2	

					CUSTOMER	CEI Conrad Electronic International(HK) Ltd		ITEM NO.	SEE THE CHART		
					PRODUCT NAME	VGA M/M CABLE		UNO ITEM NO.	UNIT	MM	
					DRAWNBY	CHECKBY		APPOBY	DATE		
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.	FERGUS					2015-11-30	