

Coil Specification (at 20 °C)

Coil Sensitivity	Nominal Voltage (VDC)	Nominal Current (mA)	Coil Resistance ($\Omega \pm 8\%$)	Power Consumption (W)	Pull-In Voltage (VDC)	Drop-Out Voltage (VDC)	Maximum Allowable Voltage (VDC)
BSVR-L	3	66.7	45	Abt. 0.2	75% Maximum	10% Minimum	130%
	5	40	125				
	6	33.7	180				
	9	22.2	405				
	12	16.7	720				
	24	8.3	2880				


Ordering Information

BSVR	-	SS	-	2	12	L
Coil Type: L:Standard DC Coil						
Coil Voltage: 03:3V, 05:5V,06:6V,09:9V 12:12V,24:24V,48:48V						
Number of Pole: 2:Two Pole						
Type of Sealing: SS:Plastic Sealed Type						
Type: BSVR						

Classification

Model	BSVR
Coil Sensitivity	Standard DC Coil 2C
Flow Solder Type	BSVR -SS-2□□L

Dimension



Dimension Tolerance: < 1mm: ± 0.2 mm

1--5mm: ± 0.3 mm

> 5mm: ± 0.5 mm