



FILE NO.	Bestell No.	UNO ITEM NO.	LENGTH
29212c33	1371918	701121.02	2000+100/-0
	1406218	701121.03	3000+100/-0
29212c82	1403826	701121.05	5000+100/-0
	1406219	701121.00	10000+100/-0

MATERIAL LIST:

⑤	HOOD MOLDED	BEIGE PVC	2	
④	SCREW	#4-40 THUMB SCREW, NICKEL PLATED	4	
③	CONNECTOR	DB 9PIN FEMALE: SOLDER TYPE, BLUE INSULATION, GOLD FLASH CONTACTS, NICKEL PLATED SHELL	1	
②	CONNECTOR	DB 9PIN MALE: SOLDER TYPE, BLUE INSULATION, GOLD FLASH CONTACTS, NICKEL PLATED SHELL	1	
①	CABLE	(28AWG BC)*9C+DRAIN TC+AM+PVC/BEIGE OD: 5.4±0.2MM	1	

NOTE:

- 100% open short & miss wire test;
- RoHS2.0 AND REACH COMPLIANT
- MARKING: COMPUTER INTERFACE CABLE 300V 80°C
- Operation temperature: -10°C ~ +60°C
Storage temperature: -20°C ~ +75°C
Operation humidity: 10%~85%
Storage humidity: 10%~85%
weight of unit (w/o packing): 29212c82: 235.5g
- PACKING: 1PCS/Renkfroce giftbox

PARTS NAME	SPECIFICATION DESCRIPTION	QT'Y	REMARK	CUSTOMER	CEI Conrad Electronic International (HK) Ltd	ITEM NO.			
	add item no 3m、10m	2015.11.30	A1	PRODUCT NAME	DB9 MALE TO FEMALE CABLE	UNO ITEM NO.	UNIT	MM	
	NEW	2015.11.26	A	DRAWNBY	CHECKBY	APPOBY	DATE		
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.	FERGUS		2015.11.26		