

**SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product identifier**

Name of product WEICONLOCK AN 306-48
Code-Nr. 306480

**1.2. Relevant identified uses of the substance or mixture and uses advised against
Recommended intended purpose(s)**

1-Component Adhesives and Sealants, anaerobic curing

1.3. Details of the supplier of the safety data sheet**Distributor**

WEICON GmbH & Co. KG
Königsberger Str. 255, DE-48157 Münster
Postbox 48045, DE-8460 Münster
Phone ++49(0)251 / 9322 - 0, Fax ++49(0)251 / 9322 - 244
E-Mail : msds@weicon.de
Internet : www.weicon.de

Advice

Produktsicherheit / Product-Safety-Department
Phone ++49(0)251 / 9322 - 0
E-mail (competent person):
msds@weicon.de

1.4. Emergency telephone number

GIZ Bonn (German, English) Tel: ++49(0)228-19 240
TRANSPORT: Consultank Lutz Harder GmbH Tel: +49(0)178
433 7434 (24h Emergency Contact)

Manufacturer

WEICON GmbH & Co. KG
Königsberger Str. 255, DE-48157 Münster

1.4. Emergency telephone number**Emergency advice**

-
Phone -
GIZ Bonn (Medizinische Auskunft in Deutsch und Englisch)
Tel: ++49(0)228-19 240
TRANSPORT: Consultank Lutz Harder GmbH Tel: +49(0)178
433 7434 (24h Emergency Contact)

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]**

Hazard classes and Hazard categories	Hazard Statements	Classification procedure
--------------------------------------	-------------------	--------------------------

Skin Irrit. 2	H315	
Eye Irrit. 2	H319	
Skin Sens. 1	H317	
STOT SE 3	H335	

Hazard Statements

H315 Causes skin irritation.

H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H335	May cause respiratory irritation.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008 [CLP/GHS]



GHS07

Signal word

Warning

Hazard Statements

H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H335	May cause respiratory irritation.

Precautionary Statements

P102	Keep out of reach of children.
P261	Avoid breathing dust/fume/gas/mist/vapours/spray.
P264	Wash hands thoroughly after handling.
P271	Use only outdoors or in a well-ventilated area.
P272	Contaminated work clothing should not be allowed out of the workplace.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P302 + P352	IF ON SKIN: Wash with plenty of soap and water.
P304 + P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P312	Call a POISON CENTER or doctor/physician if you feel unwell.
P332 + P313	If skin irritation occurs: Get medical advice/attention.
P333 + P313	If skin irritation or rash occurs: Get medical advice/attention.
P337 + P313	If eye irritation persists: Get medical advice/attention.
P362	Take off contaminated clothing.
P363	Wash contaminated clothing before reuse.
P403 + P233	Store in a well-ventilated place. Keep container tightly closed.
P405	Store locked up.
P501	Dispose of contents/container to hazardous or special waste collection point.

Hazardous ingredients for labeling

2-hydroxyethyl methacrylate, acrylic acid, cumene hydroperoxide

2.3. Other hazards

Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

**SECTION 3: Composition/ information on ingredients****3.1. Substances**

not applicable

3.2. Mixtures**Description**

Anaerobic adhesive / sealant

Hazardous ingredients

CAS No	EC No	Name	[% weight]	Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]
79-10-7	201-177-9	acrylic acid	1 < 3	Flam. Liq. 3, H226 / Acute Tox. 4, H332 / Acute Tox. 4, H312 / Acute Tox. 4, H302 / Skin Corr. 1A, H314 / Aquatic Acute 1, H400
868-77-9	212-782-2	2-hydroxyethyl methacrylate	10 - 30	Eye Irrit. 2, H319 / Skin Irrit. 2, H315 / Skin Sens. 1, H317
80-15-9	201-254-7	cumene hydroperoxide	1 < 3	Org. Perox. E, H242 / Acute Tox. 3, H331 / Acute Tox. 4, H312 / Acute Tox. 4, H302 / STOT RE 2, H373 / Skin Corr. 1B, H314 / Aquatic Chronic 2, H411

SECTION 4: First aid measures**4.1. Description of first aid measures****General information**

Remove contaminated soaked clothing immediately.

In case of inhalation

Ensure of fresh air.

In the event of symptoms refer for medical treatment.

In case of skin contact

In case of contact with skin wash off immediately with soap and water.

Consult a doctor if skin irritation persists.

In case of eye contact

In case of contact with eyes rinse thoroughly with plenty of water and seek medical advice.

In case of ingestion

Do not induce vomiting.

Refer to medical treatment.

If swallowed give water to drink.

Rinse out mouth thoroughly with water.

4.2. Most important symptoms and effects, both acute and delayed**Physician's information / possible symptoms**

vomiting

Allergic symptoms

Confusion

skin irritation

Physician's information / possible dangers

Causes serious eye damage.

4.3. Indication of any immediate medical attention and special treatment needed

No information available.



SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Alcohol-resistant foam

Dry fire-extinguishing substance

Carbon dioxide

sand

Water spray jet

Unsuitable extinguishing media

Full water jet

5.2. Special hazards arising from the substance or mixture

In case of fire formation of dangerous gases possible.

Carbon monoxide (CO)

Carbon dioxide (CO₂)

5.3. Advice for firefighters

Special protective equipment for fire-fighters

Fire-fighting operations, rescue and clearing work under effect of combustion and smoulder gases just may be done with breathing apparatus.

Do not inhale explosion and/or combustion gases.

Additional information

Cool endangered containers with water spray jet.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Ensure adequate ventilation.

Use personal protective clothing.

Keep away sources of ignition.

Use breathing apparatus if exposed to vapours/dust/aerosol.

6.2. Environmental precautions

Do not discharge into the drains/surface waters/groundwater.

Do not discharge into the subsoil/soil.

6.3. Methods and material for containment and cleaning up

Take up with absorbent material (e.g. sand, kieselguhr, acid binder, general-purpose binder, sawdust).

After taking up the material dispose according to regulation.

6.4. Reference to other sections

Safe handling: see section 7

Disposal: see section 13

Personal protection equipment: see section 8

! SECTION 7: Handling and storage

7.1. Precautions for safe handling

! Advice on safe handling

Care for thoroughly room ventilation, if necessary use in well ventilated area with local exhaust ventilation at workplace.

Take the usual precautions when handling with chemicals.



General protective measures

Do not inhale vapours.

Avoid contact with eyes and skin

Hygiene measures

At work do not eat, drink and smoke.

Remove soiled or soaked clothing immediately.

Wash hands before breaks and after work.

Advice on protection against fire and explosion

Pay attention to general rules of internal fire prevention.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep only in original container.

Advice on storage compatibility

Do not store together with animal feedstuffs.

Do not store together with food.

Do not store together with oxidizing agents.

Do not store together with reducing agents.

Do not store together with metals.

Further information on storage conditions

Store at +5 till +25 °C.

Protect from heat and direct solar radiation.

Store container at cool and aired place.

7.3. Specific end use(s)

Recommendation(s) for intended use

See section 1.2

! SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Additional advice

The statutory local and national regulations have to be observed.

8.2. Exposure controls

Respiratory protection

In case of insufficient ventilation or long-term effect use breathing apparatus.

Breathing apparatus in the event of aerosol or mist formation.

! Hand protection

In the cases of special applications, it is recommended to check the chemical resistance with the manufacturer of the gloves.

Chemical protective gloves must be chosen carefully in view of their design and depending on the dependence on the concentration and amounts of dangerous goods used in the specific working tasks.

Glove material specification [make/type, thickness, permeation time/life, wetting resistance]: fluorinated rubber; 0,7mm; 480min; 60min;

Eye protection

tightly fitting goggles

Other protection measures

protective clothing

Appropriate engineering controls

Sufficient ventilation and exhaustion.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties****Appearance**

liquid

Colour

green

Odour

hardly noticeable

Odour threshold

not determined

Important health, safety and environmental information

	Value	Temperature	at	Method	Remark
pH value	not determined				
boiling point	not determined				
melting point	not determined				
Flash point	> 100 °C				
Vapourisation rate	not determined				
Flammable (solid)	not determined				
Flammability (gas)	not determined				
Ignition temperature	not determined				
Self ignition temperature	not determined				
Lower explosion limit	not determined				
Upper explosion limit	not determined				
Vapour pressure	not applicable				
Relative density	1,1 g/ml	20 °C			
Vapour density	not determined				
Solubility in water		20 °C			more or less insoluble
Solubility/other			acetone		teilweise mischbar
Partition coefficient n-octanol/water (log P O/W)	not determined				
Decomposition temperature	not determined				
Viscosity	400 - 600 mPa*s				

Oxidising properties

No information available.

Explosive properties

No information available.



9.2. Other information
No information available.

SECTION 10: Stability and reactivity

10.1. Reactivity
No information available.

10.2. Chemical stability
No information available.

10.3. Possibility of hazardous reactions
Reactions with oxidising agents.
Reactions with reducing agents.
Reactions with Metals.

10.4. Conditions to avoid
Metal, Metal-Salts
Keep away from heat.

10.5. Incompatible materials
Substances to avoid
Oxidising agent, strong
Reducing agent, strong
Metal, Metal-Salts
Water

10.6. Hazardous decomposition products
Gases/vapours, toxic
Carbon monoxide and carbon dioxide.

Thermal decomposition

Remark No decomposition if used as directed.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity/Irritation/Sensitization

	Value/Validation	Species	Method	Remark
Skin irritation	irritant			
Eye irritation	irritant - risk of strong eye injuries			
Skin sensitization	sensitizing			

Experiences made from practice
Sensitization through skin contact possible.
Irritates eyes and skin.

Additional information
The product is to be handled with the caution usual with chemicals.
Other hazardous properties may not be excluded.
The product has not been tested. The information is derived from products of similar composition.



SECTION 12: Ecological information

12.1. Toxicity

No information available.

12.2. Persistence and degradability

No information available.

12.3. Bioaccumulative potential

No information available.

12.4. Mobility in soil

No information available.

12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

12.6. Other adverse effects

General regulation

Do not allow uncontrolled leakage of product into the environment.

Product is not allowed to be discharged into aquatic environment.

The ecotoxic effect of the product has not been tested. The information on this is given on the basis of details in the literature.

! SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste code No.

08 04 09*

Name of waste

waste adhesives and sealants containing organic solvents or other hazardous substances

Wastes marked with an asterisk are considered to be hazardous waste pursuant to Directive 2008/98/EC on hazardous waste.

! Recommendations for the product

Remove in accordance with local official regulations.

Dispose of as hazardous waste.

Recommendations for packaging

Dispose of according to the local waste regulations.

General information

Assignment to a waste code number / waste identification according to the EWC is to be carried out on a sector or process-specific basis.

SECTION 14: Transport information

	ADR/RID	IMDG	IATA-DGR
14.1. UN number	-	-	-
14.2. UN proper shipping name	-	-	-
14.3. Transport hazard class(es)	-	-	-
14.4. Packing group	-	-	-

**ADR/RID****IMDG****IATA-DGR****14.5. Environmental hazards** -

-

-

14.6. Special precautions for user

No information available.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

Transport/further information

No dangerous goods as defined by the transport regulations - ADR/RID, IMDG, ICAO/IATA-DGR.

! SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****! VOC standard****VOC content** ca.5 %**VOC value** 45,9 g/L**15.2. Chemical Safety Assessment**

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information**Recommended uses and restrictions**

National and local regulations concerning chemicals shall be observed.

For industrial use only.

Further information

Each user is responsible for the implementation of the national special regulations.

The information contained herein is based on the state of our knowledge. It characterizes the product with regard to the appropriate safety precautions. It does not represent a guarantee of the properties of the product.

Please observe the following disclaimer! --- Our safety data sheets have been compiled according to effective EU-directives, WITHOUT taking into account the special national directives concerning the handling of hazardous substances.

Indication of changes: "!" = Data changed compared with the previous version. Previous version: 8.1

H226 Flammable liquid and vapour.

H242 Heating may cause a fire.

H302 Harmful if swallowed.

H312 Harmful in contact with skin.

H314 Causes severe skin burns and eye damage.

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H319 Causes serious eye irritation.

H331 Toxic if inhaled.

H332 Harmful if inhaled.

H373 May cause damage to organs (or state all organs affected, if known) through prolonged or repeated exposure (state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard).

H400 Very toxic to aquatic life.

H411 Toxic to aquatic life with long lasting effects.