Electric	al Specification
Test Voltage	9V/ACrms
Test Current	2 mArms
Power Supply / Power adaptor	230 V/AC, 50/60 Hz
Output	9 V/AC, 100 mA
Output Frequency	50/60 Hz
Connector Size	5.5 x 2.0 mm
Power Supply	9 V/AC, max 100 mA
Typical mech	hanical specification
Lead Length	BNC test leads: 30 cm
	4mm test leads: 90 cm
Dimension	Approx. $120 \times 55 \times 24 \text{ mm}$
Weight	Approx. 180 g (without accessories
Environm	nent Specification
Operating temperature	0~40℃
Storing temperature	-10~45℃
Operating humidity	< 85% RH
Storing humidity	< 90% RH
Operating altitude	3000 m
Storing altitude	12000 m