




Type No:MC421-350
Order No:MC421-350XXZ-1

RoHS
Compliant

CE

VDE

CALUS



Pitch : 3.50mm(0.138inch)					
Poles	A(mm)	A(inch)	Poles	A(mm)	A(inch)
2	7.80	0.307	15	53.30	2.098
3	11.30	0.445	16	56.80	2.236
4	14.80	0.583	17	60.30	2.374
5	18.30	0.720	18	63.80	2.512
6	21.80	0.858	19	67.30	2.650
7	25.30	0.996	20	70.80	2.787
8	28.80	1.134	21	74.30	2.925
9	32.30	1.272	22	77.80	3.063
10	35.80	1.409	23	81.30	3.201
11	39.30	1.547	24	84.80	3.339
12	42.80	1.685	25	88.30	3.476
13	46.30	1.823			
14	49.80	1.961			

Current rating : 10Amp 300V
Insulation withstands volt : AC2000V min
Insulation resistance : >2000MΩ DC500V
Operation temperature : -40°C to +105°C
Wire strip length : 6.5mm
Wire range : 16~26 AWG
Screw torque : 3 lb-inch

	Material	Plating/Finish	Remark
1	Insulating body	Polyamide 66(UL94V-0)	Green
2	Contact	Phosphor bronze	Tin plated
3	Cage clamp	Brass	Ni plated
4	Screw	Steel	Zinc+Cr ³⁺
5			

DECA[®]SwitchLab Inc.

PART NAME

UNIT

SCALE

Terminal Blocks

MM

SHEET

1 / 1

B
REV.