

Sockets PLCC Sockets

SMT, high temperature resistance



SPECIFICATION:

Current rating: 1 A
 Insulation resistance: 1000 MΩ min.
 Contact resistance: 30 mΩ max.
 Operation temperature: -55 °C to +105 °C

MATERIAL:

Housing: PPS brown UL94V-0
 Pins: Phosphorbronze

FINISH:

Contacts: Tin plated



HANDLING:

Processing: Reflow soldering
 Packing: Tube

TOLERANCE:

.X ± 0.30
 .XX ± 0.25

RoHS
COMPLIANT



Dimensions

No. of contacts:	A:	B:	C:	D:	E:	F:
20	15.24	15.24	5.08	5.08	16.70	12.70
28	17.78	17.78	7.62	7.62	20.30	15.24
32	20.74	18.20	7.62	10.16	22.76	17.78
44	23.28	23.28	12.70	12.70	28.30	20.32
52	25.40	25.40	15.24	15.24	31.10	22.86
68	30.82	30.82	20.32	20.32	38.30	27.94
84	35.90	35.90	25.40	25.40	45.50	33.02

Order-Information

Identifier:	No. of contacts:	Version:	Packing:
PLCC	#	SMDR	#
SMT PLCC Socket	20: 20 pin 28: 28 pin 32: 32 pin 44: 44 pin 52: 52 pin 68: 68 pin 84: 84 pin	SMDR: SMT-PPS/brown	empty: Tube * R: T&R

* = standard