

VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

"Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success."

VC 63 TWO-POLE VOLTAGE TESTER

CE

VERSION 12/21

Nº 1313885

The two-pole voltage tester has been designed and tested in accordance with EN 61243-3:2010 / VDE0682 and enables reliable voltage testing on electrical equipment. The voltage is displayed via LEDs, distributed in ranges from 12 - 690 V, and as real effective value in the LCD screen (resolution 1 V).

FEATURES:

CAT III 1000V, CAT IV 600V // LED / LCD screen // Continuity test // Integrated measurement spotlight // GFCI (RCD) test function //

EQUIPMENT:

Indicator for voltage type (AC/DC), polarity and battery replacement // Optical and acoustic warning indicator for dangerous voltage (also without batteries) // Optical and acoustic continuity test // Measuring tip cover //

PACKAGE CONTENTS:

Two-pole voltage tester // 2 probe adapters (4 mm) // Probe cover // Batteries // Operating instructions //

TECHNICAL DATA:

Voltage measuring range:	12 - 690 V AC/DC
Frequency range:	0 Hz (DC), 16 - 400 Hz (AC)
Internal resistance:	200 k Ω
Power consumption:	3.5 mA (690 V)
Load connection:	30 mA (230 V)
Continuity test:	0 - 400 k Ω
Protection class:	IP64
Power supply:	2 micro-batteries (AAA)
Dimensions (L x W x H) in mm:	205 x 67 x 27
Weight:	130 g
Operating temperature:	-15°C to +45°C



Legal notice

This data sheet is published by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data sheet represent the technical status at the time of printing.

© Copyright 2022 by Conrad Electronic SE

1313885_V2_1221_01_PIX_ds