





Type No:MC101-508
Order No:MC101-508xx-1

RoHS Compliant CE VDE cULus



Pitch : 5.08mm(0.200inch)					
Poles	A(mm)	A(inch)	Poles	A(mm)	A(inch)
2	10.16	0.400	15	76.20	3.000
3	15.24	0.600	16	81.28	3.200
4	20.32	0.800	17	86.36	3.400
5	25.40	1.000	18	91.44	3.600
6	30.48	1.200	19	96.52	3.800
7	35.56	1.400	20	101.60	4.000
8	40.64	1.600	21	106.68	4.200
9	45.72	1.800	22	111.76	4.400
10	50.80	2.000			
11	55.88	2.200			
12	60.96	2.400			
13	66.04	2.600			
14	71.12	2.800			

Technical data in accordance to UL/CUL :

Current rating : 16Amp 300V (UG B)

10Amp 300V (UG D)

Insulation withstands volt : AC1600V 1 minute

Insulation resistance : >2000MΩ DC500V

Operation temperature : -40°C to +105°C

Wire strip length : 6 ~ 7mm

Wire range : 12~24 AWG

Screw torque : 7.0 lb-inch

	Material	Plating/Finish	Remark
1	Insulating body	Polyamide 66(UL94V-0)	Green
2	Contact	Phosphor bronze	Tin plated
3	Cage clamp	Brass	Ni plated
4	Screw	Steel M3	Zinc plated
5	Screw	Steel M2.6	Zinc plated

DECA[®]SwitchLab Inc.

PART NAME	UNIT	SCALE
Terminal Blocks	MM	
DRAWING NO.		SHEET
		1 / 1