

Testboy TV 328

Mould detector

Due to the dew point display, together with the mould detector, Testboy TV 328, it can find locations at risk through mould in seconds, as well as highlighting concealed and invisible thermal bridges. Due to the comprehensive performance spectrum and easy operation, it is very suitable for mobile use.

How you benefit

- | Dew point display
- | Relative humidity measurement
- | Laser ring
- | Adjustable emissivity
- | Averaging



SPECIFICATIONS

	Testboy 328
Display	LCD with backlighting
Detector	Thermopile
Measuring optic	12:1
Measurement range	-20–350 °C, 4–662 °F infrared -10–40 °C, 14–140 °F with ambient sensor
Measurement accuracy infrared	Object 10–30 °C: ±1 °C, ±1.8 °F Object -20–10 °C and 30–200°C: ±3 °C, 4 °F or ±2 %, the greater value applies
Emissivity	0.75, 0.85 and 0.95 preset
Resolution	0.1 °
Response time	< 0.5 s
Auto-Power Off	After approx. 25 s
Data-Hold function	Yes
Operating temperature	-10–40 °C, -14–140 °F
Humidity	10–90 % RH
Laser class	II, 650 nm, <1 mW
Housing	ABS synthetic material, resistant to breaking by impact
Dimensions	56 × 194 × 162 mm
Weight	222 g
Colour	Red/black
Power supply	1 × 9 V
Scope of delivery	Incl. battery and system carrying case



Thermometer/luxmeter,
moisture/range finder

