



YDPU2.E107857 Tubing, Extruded Insulating - Component

[Page Bottom](#)

Tubing, Extruded Insulating - Component

[See General Information for Tubing, Extruded Insulating - Component](#)

DSG-CANUSA GMBH

E107857

Boschstrasse 17
53359 Rheinbach, GERMANY

Cat. No.	Max V rms	Max Oper Temp, °C	Color Recognized	Oil-resistance Class[a]	VW-1 Rated[b]
Heat shrinkable flexible Polyolefin					
CFB	600	125	All except clear	None	Yes
Irradiated flexible heat shrinkable polyolefin					
CPX-100(PO-135), CPX-201, CPX-300, CRT-100, CRT-300	600	125	All except clear, w/CFR black, w/VFY, Mfr	None	No
CPX-55	600	105	All except clear	None	Yes
Heat shrinkable flexible Polyolefin					
CPX876	600	125	All except clear	None	Yes
Heat shrinkable Polyvinylidene Chloride (PVC)					
CVN-7, CVN-75	600	105	CL	None	Yes
Heat shrinkable flexible Polyolefin					
Deray-H	600	125	All except clear	None	No
Deray-I	600	125	All except clear	None	No
Deray-I 3000	600	125	All except clear	None	No
Heat shrinkable Polyvinylidene Fluoride (PVF2)					
Deray-KY175	600	150	CL	None	Yes
Heat shrinkable flexible Polyolefin					
Deray-VI	600	125	BK	None	No
Flexible heat shrinkable modified Fluoropolymer					
PO-135 HT, DERAY-HT	600	150	All except clear	None	Yes

[a] - Tubing is considered to comply with the optional Oil Resistance requirements only if authorized in the above table and marked "Oil Resistant" (or "Oil Res"), followed by the class (01, 02 or 03).

[b] - Tubing is considered to comply with the optional VW-1 flammability requirements only if authorized in the above table and if so marked.



Marking: Company name or tradename "DSG" , "E107857" or trademark , catalog designation, inside diameter (before and after recovery for heat-shrinkable tubing), voltage rating, temperature rating in degrees Celsius and date of manufacture (or traceable code) printed on tags attached to both ends of the tubing or printed on the shipping spool label or smallest unit container in which the product is packaged.

[Last Updated](#) on 2016-08-18

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2018 UL LLC".