

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

Trade name: **METABO-Pneumatikoel 46** Ref-Metabo\_0901008540 - Pneumatic Oil 0,5

Article number: 33243002

1.2 Relevant identified uses of the substance or mixture and uses advised against  
No further relevant information available.

Application of the substance / the mixture Spezialschmierstoff für gewerbliche Verwendung

### 1.3 Details of the supplier of the safety data sheet

Company: Metabowerke GmbH

Address: Metabo-Allee 1

72622 Nürtingen

Phone : +49 (0) 7022 / 720

Telefax : +49 (0) 7022 / 72 2714

1.4 Emergency telephone number: During normal opening times: ++49/2947/881-0

## SECTION 2: Hazards identification

### 2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

The substance is not classified according to the CLP regulation.

Classification according to Directive 67/548/EEC or Directive 1999/45/EC Not applicable.

Information concerning particular hazards for human and environment:

The product does not have to be labelled due to the calculation procedure of the "General Classification guideline for preparations of the EU" in the latest valid version.

Classification system:

The classification is according to the latest editions of the EU-lists, and extended by company and literature data.

### 2.2 Label elements

Labelling according to Regulation (EC) No 1272/2008 Void

Hazard pictograms Void

Signal word Void

Hazard statements Void

### 2.3 Other hazards

Results of PBT and vPvB assessment

PBT: Not applicable.

vPvB: Not applicable.

## SECTION 3: Composition/information on ingredients

### 3.2 Chemical characterisation: Mixtures

Description: Mixture of substances listed below with nonhazardous additions.

#### Dangerous components:

68649-42-3	Zinkalkyldithiophosphat	 Xi R38  N R51/53  Aquatic Chronic 2, H411  Skin Irrit. 2, H315	0.1-<1%
------------	-------------------------	--	---------

Additional information: For the wording of the listed risk phrases refer to section 16.

## SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:**  
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:**  
Rinse out mouth and then drink plenty of water.  
Do not induce vomiting; call for medical help immediately.
- **4.2 Most important symptoms and effects, both acute and delayed** Gastric or intestinal disorders
- **4.3 Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

## SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**  
Water haze  
Water spray  
Foam  
Fire-extinguishing powder  
Carbon dioxide  
CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **5.2 Special hazards arising from the substance or mixture** No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** Wear self-contained respiratory protective device.
- **Additional information**  
Gefährdete Behälter aus sicherer Entfernung mit Sprühwasser kühlen. Entweichende Dämpfe mit Wasser niederschlagen. Auf Rückzündung achten, Eindringen des Löschwassers in Oberflächen- und Grundwasser sowie Boden vermeiden. Hautkontakt durch Tragen geeigneter Schutzkleidung und durch Einhalten eines Sicherheitsabstandes vermeiden.

## SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**  
Ensure adequate ventilation  
Keep away from ignition sources.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**  
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).  
Dispose of the material collected according to regulations.
- **6.4 Reference to other sections**  
No dangerous substances are released.  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

## SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**  
Keep receptacles tightly sealed.  
Ensure good interior ventilation, especially at floor level. (Fumes are heavier than air).  
No special measures required.

Store in cool, dry place in tightly closed receptacles.

· **Information about fire - and explosion protection:** When heated the product forms flammable fumes.

· **7.2 Conditions for safe storage, including any incompatibilities**

· **Storage:**

· **Requirements to be met by storerooms and receptacles:** Store in a cool location.

· **Information about storage in one common storage facility:**

Store away from oxidising agents.

Store away from foodstuffs.

· **Further information about storage conditions:**

Protect from frost.

Protect from contamination.

Store in cool, dry conditions in well sealed receptacles.

---

---

## SECTION 8: Exposure controls/personal protection

· **Additional information about design of technical facilities:** No further data; see item 7.

· **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

· **Additional information:** The lists valid during the making were used as basis.

· **8.2 Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

The usual precautionary measures are to be adhered to when handling chemicals.

Keep away from foodstuffs, beverages and feed.

Wash hands before breaks and at the end of work.

· **Respiratory protection:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

· **Protection of hands:**

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

Recommendation: Chemical resistant protective gloves (EN 374)

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **For the permanent contact in work areas without heightened risk of injury (e.g. Laboratory) gloves made of the following material are suitable:**

Nitrile rubber, NBR

· **Eye protection:**

Safety glasses

Use safety glasses according to EN 166 : 2001.

---

---

## SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form: Fluid

· <b>Colour:</b>	Yellow
· <b>Odour:</b>	Characteristic
· <b>Odour threshold:</b>	Not determined.
· <b>pH-value:</b>	Not determined.
· <b>Change in condition</b>	
<b>Melting point/Melting range:</b>	Undetermined.
<b>Boiling point/Boiling range:</b>	Undetermined.
· <b>Flash point:</b>	> 210 °C
· <b>Flammability (solid, gaseous):</b>	Not applicable.
· <b>Ignition temperature:</b>	> 350 °C
· <b>Decomposition temperature:</b>	Not determined.
· <b>Self-igniting:</b>	Product is not selfigniting.
· <b>Danger of explosion:</b>	Product does not present an explosion hazard.
· <b>Explosion limits:</b>	
<b>Lower:</b>	Not determined.
<b>Upper:</b>	Not determined.
· <b>Vapour pressure at 20 °C:</b>	0.1 hPa
· <b>Density at 20 °C:</b>	0.875 g/cm <sup>3</sup>
· <b>Relative density</b>	Not determined.
· <b>Vapour density</b>	Not determined.
· <b>Evaporation rate</b>	Not determined.
· <b>Solubility in / Miscibility with water:</b>	Not miscible or difficult to mix.
· <b>Partition coefficient (n-octanol/water):</b>	Not determined.
· <b>Viscosity:</b>	
<b>Dynamic:</b>	Not determined.
<b>Kinematic at 40 °C:</b>	46 mm <sup>2</sup> /s V40: 46 mm <sup>2</sup> /s
· <b>Solvent content:</b>	
<b>Organic solvents:</b>	0.0 %
<b>VOC (EC)</b>	0.00 %
· <b>9.2 Other information</b>	No further relevant information available.

## SECTION 10: Stability and reactivity

- **10.1 Reactivity** Reacts with strong oxidants and strong reducing agents under severe heat.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**  
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** Temperatures above 60 °C can lead to reduced shelf life of the product.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** Flammable gases/vapours

## SECTION 11: Toxicological information

- 11.1 Information on toxicological effects
- Acute toxicity

· LD/LC50 values relevant for classification:

### 68649-42-3 Zinkalkyldithiophosphat

Oral	LD50	2230 mg/kg (rat)
Dermal	LD50	> 2000 mg/kg (rat)

- **Primary irritant effect:**
- **Skin corrosion/irritation** May cause skin irritation after repeated contact.
- **Serious eye damage/irritation** May cause slight irritation to the eyes.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

## SECTION 12: Ecological information

- 12.1 Toxicity
- **Aquatic toxicity:** No further relevant information available.
- 12.2 **Persistence and degradability** No further relevant information available.
- 12.3 **Bioaccumulative potential** No further relevant information available.
- 12.4 **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**  
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water  
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- 12.5 **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- 12.6 **Other adverse effects** No further relevant information available.

## SECTION 13: Disposal considerations

- 13.1 **Waste treatment methods**
- **Recommendation** Must be specially treated adhering to official regulations.
- **Uncleaned packaging:**
- **Recommendation:**  
Packagings that may not be cleansed are to be disposed of in the same manner as the product.

## SECTION 14: Transport information

· 14.1 UN-Number	
· ADR, ADN, IMDG, IATA	Void
· 14.2 UN proper shipping name	
· ADR, ADN, IMDG, IATA	Void

· 14.3 Transport hazard class(es)	
· ADR, ADN, IMDG, IATA	
· Class	Void
· 14.4 Packing group	
· ADR, IMDG, IATA	Void
· 14.5 Environmental hazards:	
· Marine pollutant:	No
· 14.6 Special precautions for user	Not applicable.
· 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code	Not applicable.
· UN "Model Regulation":	-

## SECTION 15: Regulatory information

- 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
- Labelling according to Regulation (EC) No 1272/2008 Void
- Hazard pictograms Void
- Signal word Void
- Hazard statements Void
- Directive 2012/18/EU
- Named dangerous substances - ANNEX I None of the ingredients is listed.
- 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

## SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

### · Relevant phrases

H315 Causes skin irritation.

H411 Toxic to aquatic life with long lasting effects.

R38 Irritating to skin.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

· **Department issuing MSDS:** Department of Environmental Health and Safety.

· **Contact:** Dr. John, Mail: labor@kajo.de

### · Abbreviations and acronyms:

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Skin Irrit. 2: Skin corrosion/irritation, Hazard Category 2

Aquatic Chronic 2: Hazardous to the aquatic environment - Chronic Hazard, Category 2

· \* Data compared to the previous version altered.