

KERN OZP 556

KERN

Professional and powerful – thanks to its extremely large magnification range, strong illumination and first-class optics



Category

Brand	Optics
Product category	Microscope
Product group	Stereo microscope
Product family	OZP-5

Construction

Dimension (W×D×H)	330×285×470 mm
Optical system	Greenough
Tube type	Binocular
Tube angle of inclination	35°
Tube 360° rotation	✓
Contrasting methods	Bright field Darkfield (optional)
Interpupillary distance [Min]	52 mm
Interpupillary distance [Max]	76 mm
Diopter adjustment	both-sided
Diopter adjustment [Min]	-6
Diopter adjustment [Max]	6

Ocular

Ocular type	Eyepiece HSWF 10x / Ø 23mm with anti-fungus, high eye point
Ocular field width	HSWF
Ocular magnifications	10x
Ocular visual field	23 mm
Ocular diameter	30 mm

Objective

Objectives magnifications	0,6x - 5,5x
---------------------------	-------------

Illumination

Illuminance	Reflected light Transmitted light
Illumination type incident light	LED
Illumination type transmitted light	LED
Illumination intensity incident light	3 W
Illumination intensity transmitted light	3 W
Illumination dimmable	Incident light + Transmitted light, separate

Focussing

Field of view [Min]	4,2 mm
Field of view [Max]	35 mm
Standard total magnification [Min]	6x
Standard total magnification [Max]	55x
Zoom [Min]	0,6x
Zoom [Max]	5,5x
Sample height [Max]	110 mm
Torque regulation	✓
Working distance	108 mm
Magnification ratio	9,2:1
Focusing mechanism	coarse drive

Stereomicroscope stand

Stand type	pillar
Diameter mounting microscope head (Ø)	76 mm

Power Supply

Supplied power supply	Power supply unit
Power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	AUS UK US CH
Input voltage power supply / power [Max]	100 - 240 V AC, 50/60 Hz, 1,0 A
Power supply cable removable	removable
Input voltage device / power [Max]	12 V, 2000 mA
Power socket for mains adapter	Inside plus, outside minus

KERN OZP 556



Professional and powerful – thanks to its extremely large magnification range, strong illumination and first-class optics

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	385×370×330 mm
Shipping method	Parcel service
Net weight approx.	4,8 kg
Gross weight approx.	6 kg
Shipping weight	9,4 kg

Product information

GTIN/EAN number	4045761169371
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

