

Type.....	57960
Designation.....	Power Bank
Systems to charge.....	Lithium-Ion / 3.7 V / 3 pcs.
Cell configurations.....	6000 mAh, 22.2 Wh
<b>Housing Material:</b> .....	ABS
<b>Dimensions:</b>	<b>Charger:</b>
Length.....	96 +- 1 mm
Width.....	64 +- 1 mm
Height.....	22 +- 1mm
Weight.....	178.5 g



<b>Charging methods:</b>	<b>Plug in Micro USB port:</b>	<b>Maintenance Charge:</b>
Input.....	Current: 1000 mA	N/A
<b>Discharging methods:</b>	<b>USB port for charging other devices</b>	
Output.....	5.0 V, 1000 mA and 2400 mA	

<b>Indications for IN:</b>	
During Charge.....	LEDs indicate level of charge and next level is flashing. LEDs flashes at the rate of 0.5 sec/cycle.
Charge completed.....	LEDs on

<b>Indications for OUT:</b>	
4 Blue LED.....	76 - 100 % Capacity
3 Blue LED.....	51 - 75 % Capacity
2 Blue LED.....	26 - 50 % Capacity
1 Blue LED.....	< 25 % Capacity

<b>Ambient temperature:</b>	
Charge.....	0 - +45 °C
Discharge.....	-20 - +45 °C
Storage.....	-20 - +45 °C

<b>Cut off criteria:</b>	
Li-Ion cells.....	Stop discharging, when Li-Ion voltage lower than 2.8 V Short circuit protection Overload protection

**No publication or circulation of data to third parties without consent of VARTA Consumer Batteries**