






## **Industry Standard Dimensions**



# **Specifications**

Classification: Alkaline

**Chemical System:** Zinc-Manganese Dioxide (Zn/MnO<sub>2</sub>)

No added mercury or cadmium

**Designation:** IEC-LR03 **Nominal Voltage:** 1.5 volts

Nominal IR: 150 to 300 milliohms (fresh)

**Operating Temp:** -18°C to 55°C **Typical Weight:** 11.5 grams

Typical Volume: 3.8 cubic centimeters


Jacket: Plastic Label

Shelf Life: 10 years at 21°C

Terminal: Flat Contact


## **Milliamp-Hours Capacity**

Continuous discharge to 0.8 volts at 21°C




# **Industry Standard Testing (21°C):**

RADIO 43 ohm 4 hrs/day



## **Battery Selection Indicator**



#### **Important Notice**

This datasheet contains typical information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

Form No. EBC - 889921POWALK Page 1 of 1