LASER SENSORS

PHOTOELECTRIC SENSORS

MICRO PHOTOELECTRIC SENSORS

> AREA SENSORS

SAFETY COMPONENTS PRESSURE

SENSORS

PARTICULAR USE SENSORS

> SENSOR OPTIONS

WIRE-SAVING SYSTEMS

MEASUREMENT SENSORS

STATIC CONTROL DEVICES

LASER MARKERS

> Selection Guide

GX-F/H

GXL GL GX-U / GX-FU / GX-N

Amplifierseparated GA-311 / GH

Other Products

Rectangular-shaped Inductive Proximity Sensor Amplifier Built-in

GX-F/H SERIES

■ Sensor selection guideP.11~ / P.647~

■ General precautions P.1012~













Industry No. 1* in stable sensing

* Based on research conducted by SUNX as of August 2007 among equivalent rectangular inductive sensors.

Can be installed with ample space

This sensor has the longest stable sensing range among the same level of rectangular inductive proximity sensors in the industry. It is easy to install the sensor.






Variation at the maximum operation distance is within ±8 %

Thorough adjustment and control of sensing sensitivity greatly reduces individual sensor differences and variations.


The work of adjusting sensor positions when using multiple sensors and when sensors have been replaced is much easier.



Temperature characteristics vary within ±8 %

Components such as the sensor coil and core and product design have been totally revised to provide excellent temperature characteristics.


Stable sensing can be obtained regardless of the time of day or the yearly season.





* Typical



APPLICATIONS








ENVIRONMENTAL RESISTANCE

10 times the durability! (Compared to previous models)

The new integrated construction method used provides shock resistance of 10,000 m/s² (approx. 1,000 G in X, Y and Z directions for three times each), and vibration resistance clears durability tests of between 10 and 500 Hz (3mm 0.118 in amplitude in X, Y and Z directions for 2 hours each). In addition, resistance to impulse noize is approx. three times greater than for previous models.




Highly resistant to water or oil! IP68g* protective construction

The new integrated construction method used improves environmental resistance performance.

The IP68g prevents damage to the sensor by stopping water and oil getting inside.

* For details, refer to the "Specifications" (p.652~)





FUNCTIONS

Indicators are easy to see over a wide field of view

A prism with a wide field of view has been developed. This has greatly improved the visibility of the operation indicators. GX-H□



Selection Guide

GX-F/H

GXL

GL

GX-U / GX-FU / GX-N

GX

Amplifierseparated

GA-311 / GH

Other Products

MOUNTING

Tightening strength increased with no damage!


A metal sleeve has been inserted. It is possible to tighten up to 0.7 N·m *.

* Maximum tightening torque for M3 screw.



Conductor thickness doubled to make wiring much easier! (GX-08 only)

The conductor's thickness was doubled for the **GX-**-8. This makes it easier to handle and perform crimping work on the cables. In addition, the tensile strength of the crimping area has become higher.





LASER

FIBER SENSORS

PHOTOELECTRIC

MICRO PHOTOELECTRIC SENSORS

AREA SENSORS

SAFETY COMPONENTS

PRESSURE SENSORS

PARTICULAR USE SENSORS

SENSOR OPTIONS

WIRE-SAVING **SYSTEMS**

MEASUREMENT

SENSORS

STATIC CONTROL DEVICES

LASER MARKERS

LASER SENSORS

PHOTO-ELECTRIC SENSORS MICRO PHOTO-ELECTRIC SENSORS

AREA SENSORS SAFETY COMPONENTS

PRESSURE SENSORS INDUCTIVE

PARTICULAR
USE
SENSORS
SENSOR
OPTIONS

OPTIONS

WIRESAVING
SYSTEMS

MEASUREMENT
SENSORS

STATIC
CONTROL
DEVICES

LASER MARKERS

GXL
GL
GX-IJ/GX-FIJ/GX-N
GX
Amplifier-separated
GA-311/GH
Other
Products

ORDER GUIDE

GX-8 type

Ту	/pe	Appearance (mm in)	Sensing range (Note 1)	Model No. (Note 2)	Output	Output operation
	Front sensing	7.4 0.29		GX-F8A	NPN open-collector	Normally open
				GX-F8AI		
=	ont s	8 0.315 0.906		GX-F8B		No II I I
NPN output	Ā			GX-F8BI		Normally closed
PN	g	~ 🔿		GX-H8A	transistor	Normally open
Z	Top sensing	9.1 0.358 8 0.315 25 0.984	Maximum operation distance 2.5 mm 0.098 in (0 to 2.1 mm 0 to 0.083 in) Stable sensing range	GX-H8AI		Normally open
				GX-H8B		Normally closed
	Ĕ			GX-H8BI		
	Front sensing	7.4 0.29 8 0.315 23 0.906		GX-F8A-P		Normally open
				GX-F8AI-P		
=				GX-F8B-P		Normally along
PNP output				GX-F8BI-P	PNP open-collector	Normally closed
	0	9.1 0.358 8 0.315 0.984		GX-H8A-P	transistor	
	sensing			GX-H8AI-P		Normally open
	Top se			GX-H8B-P		Namedical
	To			GX-H8BI-P		Normally closed

Notes: 1) The maximum operation distance stands for the maximum distance for which the sensor can detect the standard sensing object.

The stable sensing range stands for the sensing range for which the sensor can stably detect the standard sensing object even if there is an ambient temperature drift and/or supply voltage fluctuation.

2) "I" in the model No. indicates a different frequency type.

GX-12 type

Туре		Appearance (mm in)	Sensing range (Note 1)	Model No. (Note 2)	Output	Output operation
	Front sensing	7.1 0.280 12 27.8 0.472 1.094	Maximum operation distance	GX-F12A	NPN open-collector transistor	Normally open
				GX-F12AI		
¥				GX-F12B		Normally closed
NPN output				GX-F12BI		Normally closed
PN	Top sensing	13 0.512 12 0.472 1.079		GX-H12A		Normally open
Z				GX-H12AI		
				GX-H12B		Normally closed
	Ĕ	12 0.472		GX-H12BI		
	βL	7.1 0.280 12 27.8 0.472 1.094	(X) = N 1	GX-F12A-P		Normally open
PNP output	Front sensing			GX-F12AI-P		
			Stable sensing range	GX-F12B-P		Normally closed
				GX-F12BI-P	PNP open-collector	
	sensing	13 0.512 12 0.472 27.4 1.079		GX-H12A-P	4	Normally open
				GX-H12AI-P		
	Top se			GX-H12B-P		
	12		GX-H12BI-P	1	Normally closed	

Notes: 1) The maximum operation distance stands for the maximum distance for which the sensor can detect the standard sensing object.

The stable sensing range stands for the sensing range for which the sensor can stably detect the standard sensing object even if there is an ambient temperature drift and/or supply voltage fluctuation.

2) "I" in the model No. indicates a different frequency type.



OPTIONS

Designation	Model No.	Description
Sensor mounting bracket	MS-GXL8-4	Mounting bracket for GX-8 type

NPN output

Sensor mounting bracket

PNP output

• MS-GXL8-4



1 pc. each of M3 (length: 12 mm 0.472 in) truss head screw, nut, spring washer and plain washer is attached.

SPECIFICATIONS

Type |

GX-8 type

	Туре	INPIN OULPUL		PNP output	
	Front sensing	GX-F8A(I)	GX-F8B(I)	GX-F8A(I)-P	GX-F8B(I)-P
Item	Top sensing	GX-H8A(I)	GX-H8B(I)	GX-H8A(I)-P	GX-H8B(I)-P
Max. operation distance (Note 3)		2.5 mm 0.098 in ± 8 %			
Stable sensing range (Note 3)		0 to 2.1 mm 0 to 0.083 in			
Standard sensing object		Iron sheet 15 × 15 × t 1 mm 0.591 × 0.591 × t 0.039 in			
Hysteres	sis	20 % or less of operation distance (with standard sensing object)			
Repeata	bility	Along sensing axis, perpendicular to sensing axis: 0.04 mm 0.002 in or less			
Supply v	voltage		12 to 24 V DC ⁺¹⁰ ₋₁₅ %	Ripple P-P 10 % or less	
Current	consumption		15 mA	or less	
Output		Residual voltage: 1 V or le	or less (between output and 0 V)	Residual voltage: 1 V or le	100 mA or less(between output and +V) ess (at 100 mA source current) less (at 16 mA source current)
Uti	lization category		DC-12 c	2 or DC-13	
Ou	tput operation	Normally open	Normally closed	Normally open	Normally closed
Max. res	sponse frequency	500 Hz			
Operation	n indicator	Orange LED (lights up when the output is ON)			
Ро	llution degree	3 (Industrial environment)			
	otection	IP68 (IEC), IP68g (JEM) (Refer to p.1010 for details of standards.) (Note 4, 5)			
Environmental resistance	bient temperature	-25 to +70 °C -13 to +158 °F, Storage: -40 to +85 °C -40 to +185 °F			
Am	nbient humidity	45 to 85 % RH, Storage: 35 to 95 % RH			
enta	1C	EN 60947-5-2			
W Vo	Itage withstandability	1,000 V AC for one min. between all supply terminals connected together and enclosure			
ins Ins	ulation resistance	50 MΩ, or more, with 500 V DC megger between all supply terminals connected together and enclosure			
	oration resistance	10 to 500 Hz frequency, 3 mm 0.118 in amplitude in X, Y and Z directions for two hours each			
Sh	ock resistance	10,000 m/s² acceleration (1,000 G approx.) in X, Y and Z directions for three times each			
Sensing range	Temperature characteristics	Over ambient temperate	ure range –25 to +70 °C –13 to +	+158 °F: Within ± 8 % of sensing range at +23 °C +73 °F	
variation	Voltage characteristics		Within ±2 % for ⁺¹⁰ ₋₁₅ % flucti	uation of the supply voltage	
Material		Enclosure: PBT, Indicator part: Polyester			

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23 °C +73.4 °F.

2) "I" in the model No. indicates a different frequency type.

3) The maximum operation distance stands for the maximum distance for which the sensor can detect the standard sensing object. The stable sensing range stands for the sensing range for which the sensor can stably detect the standard sensing object even if there is an ambient temperature drift and/or supply voltage fluctuation.

4) SUNX's IP68 test method

Cable

Cable extension

Net weight

① Immerse at 0 m below 0 °C +32 °F water surface and leave for 30 min. Then, immerse at 0 m below +70 °C +158 °F water surface and leave for 30 min.

0.15 mm² 3-core oil, heat and cold resistant cabtyre cable, 1 m 3.281 ft long

Extension up to total 100 m 328.084 ft is possible with 0.3 mm², or more, cable.

Front sensing type: 15 g approx., Top sensing type: 20 g approx.

- 2 Regard the heat shock test in 1 as one cycle and perform 20 cycles.
- 3 Leave in water at a depth of 1 m 3.281 ft in water for 500 hours.
- 4 After tests 1 to 3, insulation resistance, voltage withstandability, current consumption, and sensing ranges must meet the standard values.
- 5) If using the sensor in an environment where cutting oil droplets splatter, the sensor may deteriorate due to added substances in the oil.



FIRFR SENSORS

LASER SENSORS

PHOTO-ELECTRIC SENSORS

AREA SENSORS

SAFETY COMPONENTS

PRESSURE SENSORS

PARTICULAR

USE SENSORS

SENSOR OPTIONS

WIRE-SAVING SYSTEMS MEASURE-MENT SENSORS

STATIC CONTROL DEVICES

LASER MARKERS

Selection Guide

GXL

GL GX-U / GX-FU / GX-N

GX

Amplifier-separated GA-311 / GH

LASER SENSORS

PHOTO-ELECTRIC SENSORS MICRO PHOTO-ELECTRIC SENSORS

AREA SENSORS SAFETY COMPONENTS

PRESSURE SENSORS

PARTICULAR SENSORS

SENSOR OPTIONS SAVING SYSTEMS MEASURE-MENT SENSORS

STATIC CONTROL DEVICES LASER MARKERS

GXL GL GX-U / GX-FU / GX-N GX

Amplifier-separated GA-311 / GH Other Products

SPECIFICATIONS

GX-12 type

		Туре	NPN (output	PNP (output	
	\ :	2	So Front sensing	GX-F12A(I)	GX-F12B(I)	GX-F12A(I)-P	GX-F12B(I)-P
Item		Top sensing	GX-H12A(I)	GX-H12B(I)	GX-H12A(I)-P	GX-H12B(I)-P	
Max. o	perat	ion distance (Note 3)		4.0 mm 0.1	58 in ± 8 %		
Stable	sens	sing range (Note 3)		0 to 3.3 mm	0 to 0.130 in		
Standa	ard s	ensing object		Iron sheet 20 × 20 × t 1 mn	1 0.787 × 0.787 × t 0.039 in		
Hyster	resis		20 % or less of operation distance (with standard sensing object)				
Repea	atabili	ty	Along sensing axis, perpendicular to sensing axis: 0.04 mm 0.002 in or less				
Supply	y volt	age		12 to 24 V DC ⁺¹⁰ ₋₁₅ %	Ripple P-P 10 % or less		
Curren	nt cor	nsumption		15 mA	or less		
Output			Residual voltage: 1 V or le	or less (between output and 0 V)	PNP open-collector transistor • Maximum source current: 100 mA • Applied voltage: 30 V DC or less(between output and + • Residual voltage: 1 V or less (at 100 mA source curren 0.4 V or less (at 16 mA source curren		
ι	Jtiliza	ation category		DC-12 c	or DC-13		
C	Outpu	it operation	Normally open	Normally closed	Normally open	Normally closed	
Max. response frequency		nse frequency	500 Hz				
Operat	tion i	ndicator	Orange LED (lights up when the output is ON)				
F	Pollution degree		3 (Industrial environment)				
e F	Protection		IP68 (IEC), IP68g (JEM) (Refer to p.1010 for details of standards.) (Note 4, 5)				
Environmental resistance	Ambie	ent temperature	–25 to +70 °C −13 to +158 °F, Storage: –40 to +85 °C −40 to +185 °F				
resi	Ambie	ent humidity	45 to 85 % RH, Storage: 35 to 95 % RH				
ental	EMC		EN 60947-5-2				
uno V	/oltag	ge withstandability	1,000 V AC for one min. between all supply terminals connected together and enclosure				
in ir	Insulation resistance		50 M Ω , or more, with 500 V DC megger between all supply terminals connected together and enclosure				
	Vibration resistance		10 to 500 Hz frequency, 3 mm 0.118 in amplitude in X, Y and Z directions for two hours each				
S	Shock	c resistance			x.) in X, Y and Z directions for three times each		
Sensing range variation		Temperature characteristics	Over ambient temperature range –25 to +70 °C –13 to +158 °F: Within ±8 % of sensing range at +23 °C +73 °C			range at +23 °C +73 °F	
		Voltage characteristics	Within ± 2 % for $^{+10}_{-15}$ % fluctuation of the supply voltage				
Material			Enclosure: PBT, Indicator part: Polyester				
Cable			0.15 mm² 3-core oil, heat and cold resistant cabtyre cable, 1 m 3.281 ft long				
Cable extension		nsion	Extension up to total 100 m 328.084 ft is possible with 0.3 mm², or more, cable.				
Net weight			Front sensing type: 20 g approx., Top sensing type: 20 g approx				


Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23 °C +73.4 °F.

- 2) "I" in the model No. indicates a different frequency type.
- 3) The maximum operation distance stands for the maximum distance for which the sensor can detect the standard sensing object. The stable sensing range stands for the sensing range for which the sensor can stably detect the standard sensing object even if there is an ambient temperature drift and/or supply voltage fluctuation.
- 4) SUNX's IP68 test method
 - (1) Immerse at 0 m below 0 °C +32 °F water surface and leave for 30 min. Then, immerse at 0 m below +70 °C +158 °F water surface and leave for 30 min.
 - ② Regard the heat shock test in ① as one cycle and perform 20 cycles.

 - ③ Leave in water at a depth of 1 m 3.281 ft in water for 500 hours.
 ④ After tests ① to ③, insulation resistance, voltage withstandability, current consumption, and sensing ranges must meet the standard values.
- 5) If using the sensor in an environment where cutting oil droplets splatter, the sensor may deteriorate due to added substances in the oil.

I/O CIRCUIT DIAGRAMS


GX-□ NPN output type



Note: The output does not incorporate a short-circuit protection circuit. Do not connect it directly to a power supply or a capacitive load.

Symbols ... D : Reverse supply polarity protection diode ZD1, ZD2: Surge absorption zener diode Tr : NPN output transistor

GX-□-P PNP output type



Note: The output does not incorporate a short-circuit protection circuit.


Do not connect it directly to a power supply or a capacitive load.


Symbols ... D : Reverse supply polarity protection diode ZD: Surge absorption zener diode Tr: PNP output transistor

SENSING CHARACTERISTICS (TYPICAL)

GX-8 type

Sensing field







As the sensing object size becomes smaller than the standard size (iron sheet $15 \times 15 \times t$ 1 mm $0.591 \times 0.591 \times t$ 0.039 in), the sensing range shortens as shown in the left figures.


GX-12 type

Sensing field





Correlation between sensing object size and sensing range



As the sensing object size becomes smaller than the standard size (iron sheet $20 \times 20 \times t$ 1 mm $0.787 \times 0.787 \times t$ 0.039 in), the sensing range shortens as shown in the left figure.

FIBER SENSORS

LASER SENSORS

PHOTO-ELECTRIC SENSORS MICRO PHOTO-ELECTRIC SENSORS

AREA SENSORS

SAFETY COMPONENTS

PRESSURE SENSORS

PARTICULAR USE SENSORS

SENSOR OPTIONS

WIRE-SAVING SYSTEMS

MEASURE-MENT SENSORS

CONTROL

LASER MARKERS

Selection Guide Amplifier Built-in

GX-F/H

GL

GX-U / GX-FU GX-N

Amplifierseparated

GA-311 / GH Other

LASER SENSORS

PHOTO-ELECTRIC SENSORS

MICRO PHOTO-ELECTRIC SENSORS

AREA SENSORS SAFETY COMPONENTS

PRESSURE SENSORS

PROXIMITY SENSORS PARTICULAR

> SENSORS SENSOR OPTIONS

WIRE-SAVING SYSTEMS MEASURE-MENT SENSORS

STATIC CONTROL DEVICES LASER MARKERS

Selection Guide Amplifier Built-in

GXL
GL
GX-U/GX-FU/
GX-N
GX

Amplifierseparated GA-311/GH

Products

PRECAUTIONS FOR PROPER USE

Refer to p.1012~ for general precautions.




 Never use this product as a sensing device for personnel protection.

 In case of using sensing devices for personnel protection, use products which meet laws and standards, such as OSHA, ANSI or IEC etc., for personnel protection applicable in each region or country.

Mounting


GX-8 type

• Make sure to use a M3 (length: 12 mm 0.472 in or more) truss head screw. The tightening torque should be 0.7 N·m or less. /Do not use a flat head screw or a pan head screw.




GX-12 type

- The tightening torque should be 0.7 N·m or less.
- To mount the sensor with a nut, the mouting hole diameter should be Ø3.4 mm Ø0.134 in. Further, the hole in which the boss is inserted should be Ø2.5 mm Ø0.098 in and 3 mm 0.118 in, or more, deep.




Influence of surrounding metal

 When there is a metal near the sensor, keep the minimum separation distance specified below.



GX-F8□	GX-F12□
7.4 mm 0.291 in	7.1 mm 0.280 in
8 mm 0.315 in	20 mm 0.787 in
3 mm 0.118 in	7 mm 0.276 in
	7.4 mm 0.291 in 8 mm 0.315 in

Top sensing type




	GX-H8□	GX-H12□
D	4 mm 0.157 in	7 mm 0.276 in
Е	10 mm 0.394 in	20 mm 0.787 in
F	3 mm 0.118 in	3 mm 0.118 in
G	3 mm 0.118 in	3 mm 0.118 in

Mutual interference prevention

 When two or more sensors are installed in parallel or face to face, keep the minimum separation distance specified below to avoid mutual interference.

	Н	J	
GX-F8⊓	Between "I" type and non "I" type	0 mm (Note 2)	15 mm 0.591 in
GX-FOL	Between two "I" types or two non "I" types	20 mm 0.787 in	35 mm 1.378 in
GX-H8⊓	Between "I" type and non "I" type	0 mm (Note 2)	15 mm 0.591 in
GХ-По⊔	Between two "I" types or two non "I" types	20 mm 0.787 in	35 mm 1.378 in
GX-F12	Between "I" type and non "I" type	0 mm (Note 2)	25 mm 0.984 in
GX-H12□	Between two "I" types or two non "I" types	25 mm 0.984 in	50 mm 1.969 in



Notes: 1) "I" in the model No. specifies the different frequency type.

Close mounting is possible for up to two sensors.
 When mounting three sensors or more at an equal spacing, align the model with "!"

When mounting three sensors or more at an equal spacing, align the model with "I" and the model without "I" alternately. The minimum value of dimension "H" should be as given below.

GX-8 type: 6mm 0.236 in

GX-8 type: 6mm 0.236 in **GX-12** type: 6.5mm 0.256 in

Sensing range

 The sensing range is specified for the standard sensing object. With a non-ferrous metal, the sensing range is obtained by multiplying with the correction coefficient specified below. Further, the sensing range also changes if the sensing object is smaller than the standard sensing object or if the sensing object is plated.

Correction coefficient

Correction Coefficient				
Model No. Metal	GX-8 type	GX-12 type		
Iron	1	1		
Stainless steel (SUS304)	0.76 approx.	0.79 approx.		
Brass	0.50 approx.	0.56 approx.		
Aluminum	0.48 approx.	0.53 approx.		

Others

- The output does not incorporate a short-circuit protection circuit. Do not connect it directly to a power supply or a capacitive load.
- Do not use during the initial transient time (50 ms) after the power supply is switched on.


DIMENSIONS (Unit: mm in) The CAD data in the dimensions can be downloaded from the SUNX website: http://www.sunx.com

GX-H8□

GX-F8□ Operation indicator (Orange) 2.95 Sensing 8.55 direction 7.7 23 0.906 11.5 0.453 22.5 .45. <u>▼</u>
6.5 ø3.1 ø0.12 mounting hole 9.75 0 ø3 ø0.118 cable, 1 m 3.281 ft long 2.65 5.4 0.039 0.209


GX-F12□ Senso

Operation indicator (Orange) - 3.3 <mark>0.130</mark> -1.5 0.059 Sensing ø2.3 direction 27.8 27 11.05 16 0.630 16 ø3.1 ø0.12 mounting hole 12.4 5 0.197 ø6 ø0.236 screw seat, 0.8 0.032 deep 4.4 0.173 1 ø3 ø0.118 cable, 1 m 3.281 ft long 6.8 0.268 2.8 110 5.2 0. 5.6




MS-GXL8-4

Sensor mounting bracket for **GX-8 type** (optional)



Mounting hole dimensions



Material: Stainless steel (SUS304)

1 pc. each of M3 (length 12 mm 0.472 in) truss head screw, nut, spring washer and plain washer are attached.

FIBER SENSORS

LASER SENSORS

PHOTO-ELECTRIC SENSORS

MICRO PHOTO-ELECTRIC SENSORS AREA SENSORS

SAFETY COMPONENTS

PRESSURE SENSORS

INDUCTIVE

PARTICULAR USE SENSORS

> SENSOR OPTIONS

WIRE-SAVING SYSTEMS MEASURE-MENT SENSORS

STATIC CONTROL DEVICES

LASER MARKERS

> Selection Guide

> > Built-in GX-F/H

GXL

GL GX-U / GX-FU / GX-N

GX Amplifier-

Amplifierseparated GA-311 / GH

Other Products