

ENERGIZER A544




ZEROMERCURY®

Miniature Alkaline

Specifications

Chemical System:	Manganese Dioxide (MnO ₂)
Designation:	ANSI/NEDA-1414A, IEC-4LR44
Nominal Voltage:	6.0 volts
Typical Weight:	9.8 grams (0.3 oz)
Typical Volume:	3.3 cubic centimeters (0.2 cubic inch)
Typical Capacity:	152 mAh to 3.6 volts (rated at 27k ohms at 21°C)
Cells:	Four No. LR44 in series
Jacket:	Metal

Industry Standard Dimensions



Designed specifically for photo use


Typical Discharge Characteristics

21°C (70°F)

Schedule (time)	Drain (mA)	Load (ohms)	Cutoff Voltage
			3.6V (hours)
Continuous	0.187	27K	910

Discharge Characteristics

Schedule: Continuous
Typical Load: 27K ohms (21°C)



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.
Contents herein do not constitute a warranty and are for reference only.