


# ENERGIZER EPX625G

**Miniature Alkaline**



## Industry Standard Dimensions




Designed specifically for photo use

## Typical Discharge Characteristics

21°C (70°F)

**Load: 2.5K ohms - Continuous**  
**Typical Drain @ 1.25V: 0.5 mA**




| Schedule:  | Typical Drains:<br>at 1.25V<br>(milliamperes) | Load<br>(ohms) | Cutoff<br>0.9V<br>(hours) |
|------------|-----------------------------------------------|----------------|---------------------------|
| Continuous | 0.5                                           | 2,500          | 355                       |

## General Information

|                          |                                                            |
|--------------------------|------------------------------------------------------------|
| <b>Chemical System:</b>  | Manganese Dioxide (MnO <sub>2</sub> )                      |
| <b>Designation:</b>      | N/A                                                        |
| <b>Nominal Voltage:</b>  | 1.5 Volts                                                  |
| <b>Typical Capacity:</b> | 175 mAh (to 0.9 volts)<br>Rated at 2.5K ohms / 21°C (70°F) |
| <b>Typical Weight:</b>   | 3.3 grams (0.12 ounces)                                    |
| <b>Typical Volume:</b>   | 1.2 cubic centimeters (0.07 cubic inch)                    |

## Cross Section



### Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.  
**Contents herein do not constitute a warranty and are for reference only.**