



VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

VC 12/24V 3.1A DUAL USB CAR ADAPTER

Nº 1434061

CE

VERSION 12/21

This USB car adapter is suitable for charging up to 2 USB devices simultaneously. Power is supplied via an on-board voltage socket. The current readings (car battery voltage, current consumption, and temperature) will be shown on the LED display alternately for 10 seconds each.

HIGHLIGHTS

Measuring car battery voltage, current consumption, and temperature //

Suitable for charging smartphones, MP3 players, etc. inside a vehicle //

2 USB charging ports //

Output 5 V/DC, 3.1 A (total) //

Input 12 - 24 V //

LED display //



TECHNICAL DATA

Input voltage	12 – 24 V/DC
Output voltage/current	5 V/DC, 3.1 A (total)
Output current per each port	2.4 A (at 12 V/DC) 2.1 A (at 24 V/DC)
Measurement range	car battery voltage: 5 – 25 V/DC current consumption: 0 – 3.1 A temperature: -20 to +80 °C
Operating conditions	0 to +45 °C, 35 – 85 % RH
Storage conditions	-20 to +70 °C, 5 – 95 % RH
Dimensions (L x W x H)	78 x 42 x 32 mm
Weight	25 g

PACKAGE CONTENT

USB adapter // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).
All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.