

# Identification Systems

## Report Generating Accessories

3-349-475-03  
11/3.14

### Z502F, Z720A and Z751A Barcode Scanners

- Scanning distances of up to 20 cm
- Green Spot technology

### Z721D Barcode Printer

- High speed device
- Can be integrated into networks

### Z751G RFID Read / Write

- Combined read and write system for 13.56 MHz transponders
- RS 232 interface

### Z751E RFID Read / Write

- Combined read and write system for 13.56 MHz transponders
- USB-HID interface

### Thermal Printer Z721S

- Thermal line dot printer for text
- USB interface



## Application

Barcode and RFID identification systems are used to mark and identify tools and equipment.

The scanning devices are exclusively matched to the interfaces included with SECUTEST, PROFITEST, MINITEST, SECUSTAR and SECULIFE test instruments. They forward the scanned code to the respective test device in order to be able to allocate measured values and test results to the device under test in an unequivocal fashion.

ID numbers can be written to RFID tags with the SCANBASE RFID devices (Z751G and E). ID numbers can be printed onto barcode labels with the barcode printer and a PC.

## Features

### Z720A and Z751A Barcode Scanners

These devices are based upon the concept of an instinctive scanning distance and provide best possible reading performance at distances of up to 20 cm. Green Spot technology projects "good-read" indication directly onto the code. The Z720A is equipped with an RS 232 port, and the Z751A with a USB port.

### Z721D Barcode Printer

High performance, fast, PC compatible labeling system. Prints especially high quality, durable labels. The device is particularly well suited for printing resilient barcode labels.

### Z751G SCANBASE RFID: RFID Reader / Writer

Compact reading and writing device with RS 232 port for programming and reading 13.56 MHz transponders in accordance with ISO15693.

### Z751E SCANBASE RFID: RFID Reader / Writer

Compact reading and writing device with USB port for programming and reading 13.56 MHz transponders in accordance with ISO15693.

## Applicable Regulations and Standards

**DIN EN 61326**  
**VDE 0843, part 20**

Electrical equipment for control technology and laboratory use – EMC requirements

# Identification Systems

## Report Generating Accessories


### Device Overview


					
<b>Designation</b>	<b>Barcode Scanner</b>			<b>RFID Read/Write</b>	<b>RFID Read/Write</b>
Type	Z720A	Z502F	Z751A	SCANBASE RFID	SCANBASE RFID
Feature Article no.	Z720A	Z502F	Z751A	Z751E <sup>2)</sup>	Z751G <sup>2) 3)</sup>
Connection interfaces	RS232	RS232	USB	USB-HID	RS232
Connection cable (2 m)	stright	coiled	stright	stright	stright
Frequency	—			13.56 MHz	
Readable codes (selection), RFID tags	Code 39, code 128, EAN 13 (12 digits) <sup>1)</sup>			ISO15693, Z751R, Z751S, Z751T	
Scanning distance	Max. 210 mm			Approx. 30 mm	Approx. 30 mm
Power supply	Via interface			Via interface	
Operating temperature	0 °C ... 55 °C			-10 °C ... 55 °C	
Dimensions	195 x 70 x 66 mm			240 x 120 x 35 mm	
Usable for following devices and product ranges	SECUTEST PSI, SI, SI+, SECUSTORE PROFITEST (P)SI-BC, PROFITEST 204 PROFITEST M ..., MINITEST MASTER, MINITEST 3P MASTER, SECUTEST SII+, SECUTEST SIII+, SECUTEST 3PL, SECULIFE ST		SECUSTAR FM, SECULIFE SB SECUTEST BASE(10) / XTRA	SECUSTAR FM, SECULIFE SB	MINITEST MASTER, MINITEST 3P MASTER, SECUTEST SII+, SECUTEST SIII+, SECUTEST 3PL, SECULIFE ST, PROFITEST 204 PROFITEST M ..., SECUSTORE

<sup>1)</sup> Z720A and Z751A have the appropriate scanning width to be programmed to the EAN 128 barcode.

<sup>2)</sup> In order to program the RFID tags, the respective RFID scanner/programmer must be connected to the PC by using the software which is available on the attached CD ROM.






<sup>3)</sup> Please note: Z751GA requires a special RS232 cable and power supply unit which are both available from our Customer Service Center. The contact address is given on the last page.

	
<b>Designation</b>	<b>Barcode Printer</b>
Type	Z721D
Feature Article no.	Z721D
Connection interfaces	To the PC: USB, serial
Text entry	Via PC keyboard
Fonts	All of the computer's true type fonts
Font sizes	1.2 to 27 mm
Label tape	TZ, AL, HG
Label tape width	6, 9, 12, 18, 24, 36 mm (TZ/HG), 24 mm (AL)
Print resolution	360 dpi
Printing speed	Up to 80 mm per second
Power supply	Power pack
Weight	1.6 kg
Dimensions	116 x 192 x 140 mm

	
<b>Designation</b>	<b>Thermal Printer for SECUTEST BASE(10)/XTRA</b>
Type	Z721S
Feature Article no.	Z721S
Connection interfaces	To the PC: USB, IrDA, serial
Method	Thermal line dot printing
Fonts	Extended graphics character set
Paper width	112 mm
Printing width	104 mm
Print resolution	8 Pixel/mm
Printing speed	90 mm/s
Power supply	Power supply adapter with mains cable
Weight	0,5 kg
Dimensions	15 x 14 x 6 cm (W x D x H)

# Identification Systems Report Generating Accessories

## Accessories Overview

				No photo		
<b>Designation</b>	<b>RFID Tag</b>				<b>Label Tape Cartridge</b>	
Type	Z751R	Z751S	Z751T	ZxxxX	Z722D	Z722E
Feature Article no.	Z751R	Z751S	Z751T	ZxxxX	Z722D	Z722E
Usable for following devices	Z751E, Z751G				Z721D	
Frequency	13.56 MHz			125 kHz	—	
Chip	ICODE SLI with 1 kBit data memory				—	
Writing cycles	100,000				—	
Reading cycles	Unlimited				—	
Material	ABS				—	
Temperature range	-20 ° to +60 °C				—	
Standard	ISO 15693			HITAG1, 2, S, Q5, Titan, Atmel5577, EM-4XXX	—	
Type	Dia. approx. 22 mm, self-adhesive (the photos show the front, as well as the adhesive back)	Dia. approx. 30 mm thickness 2 - 3 mm with 3 - 4 mm hole	Pigeon ring, dia. approx. 10 mm	Upon request	Cartridge	
Quantity per package	500 pieces		250 pieces	1000 pieces	1 set of labels includes the following label tape cartridges: 3 x 24 mm wide, 1 x 18 mm wide, 1 x 9 mm wide, length: 8 m each	1 set of labels includes the following label tape cartridges: 5 x 18 mm wide, length: 8 m each

# Identification Systems

## Report Generating Accessories

### Order Information

Description	Type	Article Number
<b>Barcode Scanners</b>		
Barcode scanner for RS 232 connection (laser sensor), variable barcode length, enhanced reading accuracy	Z720A	Z720A
Barcode scanner for RS 232 connection (laser sensor), variable barcode length, enhanced reading accuracy, with coil-cable	Z502F	Z502F
Barcode scanner for USB connection	Z751A	Z751A
<b>Barcode Printer</b>		
Barcode and label printer including software, for USB and RS232 connection to the PC	Z721D	Z721D
<b>Accessories</b>		
Label set for Z721D barcode and label printer (quantity x width: 3 x 24, 1 x 18, 1 x 9 mm, length: 8 m each)	Z722D	Z722D
Label set for Z721D barcode and label printer (qty. x width: 5 x 18 mm, 8 m long each)	Z722E	Z722E
<b>RFID Readers / Scanners</b>		
RFID read/write for USB connection (frequency: 13.56 MHz)	SCANBASE RFID	Z751E
RFID read/write for RS 232 connection (13.56 MHz)	SCANBASE RFID	Z751G
<b>Accessories</b>		
RFID tags per ISO 15693, dia. approx. 22 mm, self-adhesive, 500 pcs.	Z751R	Z751R
RFID tags per ISO 15693, dia. approx. 30 mm, thickness 2 - 3 mm with 3 - 4 mm hole 500 pcs.	Z751S	Z751S
RFID tags per ISO 15693, pigeon ring, dia. approx. 10 mm, 250 pcs.	Z751T	Z751T
RFID tag (125 kHz), shape as requested, 1000 pcs.	ZxxxX	ZxxxX
<b>Thermal printer for SECUTEST BASE(10)/XTRA</b>		
Thermal printer for printing out test reports; inkl. manual on CD, Lithium-Batterie, power supply adapter, mains cable, 1 roll of Thermopaper	Z721S	Z721S
<b>Accessories</b>		
Thermo paper for Z721S; 10 roll of thermo paper, Ø 12/50mm, 30 m x 112 mm, coating outside	Z722S	Z722S

For additional information regarding accessories please refer to:

- The data sheet for the respective device or our Measuring Instruments and Testers catalogue.
- [www.gossenmetrawatt.com](http://www.gossenmetrawatt.com)