



MP1250

Nominal Voltage (V) 12V

Nominal Capacity

20hour rate (0.17A to 10.50V)	2Ah
10hour rate (0.16A to 10.50V)	2Ah
5hour rate (0.56A to 10.20V)	1.7Ah
1C (3.3A to 9.60V)	0.9Ah
3C (9.9A to 9.60V)	0.72Ah

Weight 0.65kg(1.43Lbs.)

Internal Resistance (at 1KHz) 105 mΩ

Maximum Discharge Current for 30 seconds : 40A

Maximum Discharge Current for 5 seconds : 80A

Operating Temperature Range

Charge	0°C (32°F) to 40°C (104°F)
Discharge	-15°C (5°F) to 50°C (122°F)
Storage	-15°C (5°F) to 40°C (104°F)

Charge Retention (shelf life) at 20°C (68°F)

1 month	92%
3 month	90%
6 month	80%

Charging Methods at 25°C (77°F)

Cycle use:

Charging Voltage 14.4 to 15.0V
Maximum Charging Current: 0.6A

Standby use:

Float Charging Voltage 13.50 to 13.80V

Life expectancy :

Cycle Use:

- 100% depth of discharge 200 cycles
- 80% depth of discharge 225 cycles
- 50% depth of discharge 500 cycles

Standby Use: 3-5 years

Case Material ABS
(Option: 94-HB & 94V-0 flame retardant case)

Terminal F13

