

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“For more than 25 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

DL-200T DATA LOGGER



VERSION 08/16

Nº 1435090

The battery-operated portable data logger has an internal temperature sensor. Measuring temperature data is recorded automatically at adjustable sampling rates from 1 minute to 24 hours. At most 40,020 measuring values can be saved. Measured values can be immediately read on the LC display. It automatically generates a graphical report in PDF format.

HIGHLIGHTS

USB stick design // Max./Min. readings //

IP65 ingress protection with protective cap //

Configuration via website or software//

TECHNICAL DATA

Power supply	1 x 3 V button cell, type CR2450
Battery life.	1 year (for sampling rate 1 time/min)
Protection type	IP65
Connector type	USB 2.0
Sampling rate	1 minute - 24 hours
Measured value	temperature
Memory capacity	40020 for temperature data
Resolution	0,1 °C
Temperature measuring range	-30 to +60 °C
Temperature accuracy	+/- 0,5 °C (>0 to +60 °C) +/- 1 °C (-30 to 0 °C)
Dimensions (W x H x D)	approx. 37 x 86 x 19 mm
Weight	approx. 42 g (including button cell)



PACKAGE CONTENT

Data logger incl. USB protective cap // 3 V button cell, type CR2450 // Software CD // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.