

**SINGLE BEVEL**

◀ **120 mm** ▶

**60 mm**

◀ **1500 W**

  
**210 mm**

**LASER**



**SPECIFICATIONS**

Dimensions L x W x H	690 x 550 x 440 mm
Blade Ø	210 mm
Blade speed	5000 rpm
Bevel type	1 x 45°
Mitre capacity	45° left – 45° right
Cross cut at 90°	120 x 60 mm
Mitre cut at 45°	80 x 60 mm
Mitre slots	45-30-22.5-15-0-15-22.5-30-45°
Weight	7.7 kg
Motor	220 – 240 V
Input	1500 W
Order No	3901105915
Barcode	4046664017028

**HM80L | 8" COMPOUND MITRE SAW**

THIS MODEL IS A SMALL, ECONOMIC MITRE SAW FOR THE DIY ENTHUSIAST DOING OCCASIONAL CUTS. WITH ITS FULLY MACHINED ALUMINIUM BASE, IT IS LIGHT AND THEREFORE EASILY TRANSPORTED. DESPITE ITS LIGHT WEIGHT, HOWEVER, THE HM80L IS VERSATILE, PERMITTING THE EXECUTION OF EXACT MITRE, BEVEL AND COMPOUND CUTS WITH THE HELP OF THE SCALES ON TABLE AND ARM.

- Lightweight die cast aluminium design for easy transport
- Powerful 1.5 kW Motor provides various cutting applications
- Compact bench top design fits conveniently in small shop environments
- The 24-teeth carbide tipped blade stays sharp and makes clean cuts
- BIG cross cut capacity up to 120 mm
- Fully enclosed blade guard for operator safety
- Torsion resistant design and top quality construction

**LOGISTICAL DATA**

20 Container	500 pcs
40 Container	N. A.
40 HQ Container	1200 pcs