

INDUCTION MOTOR

150 mm 370 W



PERFECT
SANDING
RESULTS

BTS800 | 6" BELT AND DISC SANDER

MULTIFUNCTIONAL AND HANDY, THIS COMBINATION BELT AND DISC SANDER DELIVERS POWER TO MAKE ALMOST ANY SANDING PROJECTS MEET YOUR EXPECTATIONS.

- Induction motor delivers powerful, quiet, dependable performance
- The belt sander unit can be adjusted by 90° from vertical to horizontal position.
- The sanding table, swinging through 45°, can variably be used for belt and disc sanding.
- The cast-iron base keeps the sander stable during use, so you can apply the desired amounts of pressure and achieve consistent results.
- The sanding discs are easily attached with the velcro fastening system.



LOGISTICAL DATA

20 Container	505 pcs
40 Container	1008 pcs
40 HQ Container	1008 pcs

SPECIFICATIONS

Dimensions L x W x H	470 x 360 x 330 mm
Sanding belt length / width	915 / 100 mm
Sanding disc	150 mm
Table adjustment	90° – 45°
Belt speed	7.5 m/sec.
Sanding disc speed	2850 rpm
Suction connector Ø	63 mm
Weight	22.5 kg
Motor	230 V
Input	370 W
Order No	4903302901
Barcode	4014915082095