

## Housing - HC-EVO-B10-CHWS-PLRBK - 1407640

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON EVO coupling housing, plastic, with bayonet flange for EVO screw connection, B10, with single locking latch, height: 90 mm, without EVO screw connection

### Your advantages

- Flexible cable outlet direction, lateral or straight
- Lower costs than metal version
- Labeling option using 9 x 20 mm marking label
- Low weight
- Lower risk of condensation
- Both contact insert PE sheets are connected by means of a metal frame integrated in the sleeve housing
- Metal inlays ensure leading PE contact with angled plugs
- Completely corrosion-resistant
- Halogen-free plastic
- Impact test according to IK 08
- Marking label can be attached

### Key commercial data

package_quantity	1
GTIN	4046356777025

### Technical data

#### Dimensions

Height	90 mm
Width	44 mm
Length	73 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP66
Degree of protection of housing (NEMA)	4 (NEMA 250)
Degree of protection of housing (NEMA)	4X (NEMA 250)
Degree of protection of housing (NEMA)	12 (NEMA 250)
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Note	For contact inserts HC-B10, BB18, DD42, M, K8/24, HV03-I-PT, HC- 3-E...C
------	--

# Housing - HC-EVO-B10-CHWS-PLRBK - 1407640

## Technical data

### General

<b>Size</b>	B10
<b>Housing type</b>	Coupling housings
<b>Color</b>	black
<b>Locking type</b>	With single locking latch
<b>No. of cable outlets</b>	1
<b>Cable exit</b>	straight
<b>Cable exit</b>	Lateral
<b>Screw connection</b>	none
<b>Housing material</b>	Polyamide
<b>Seal material</b>	NBR
<b>Material lock</b>	Polyamide
<b>Flammability rating according to UL 94</b>	V0
<b>Connection</b>	The coupling housing must be supplemented with the EVO screw connection. The EVO screw connection is available in four sizes. The EVO screw connection is mounted with the aid of a pipe wrench, for example.

### Standards and Regulations

<b>Flammability rating according to UL 94</b>	V0
---	----

### Classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	27140816
<b>eCl@ss 4.1</b>	27140816
<b>eCl@ss 5.0</b>	27143424
<b>eCl@ss 5.1</b>	27143424
<b>eCl@ss 6.0</b>	27143424
<b>eCl@ss 7.0</b>	27440209
<b>eCl@ss 8.0</b>	27440202
<b>eCl@ss 9.0</b>	27440202

#### ETIM

<b>ETIM 3.0</b>	EC000437
<b>ETIM 4.0</b>	EC000437
<b>ETIM 5.0</b>	EC000437

#### UNSPSC

<b>UNSPSC 6.01</b>	31261502
<b>UNSPSC 7.0901</b>	31261502
<b>UNSPSC 11</b>	31261502
<b>UNSPSC 12.01</b>	31261502
<b>UNSPSC 13.2</b>	31261502

# Housing - HC-EVO-B10-CHWS-PLRBK - 1407640

## Approvals

---

GL / EAC /

---

### Approval details

GL s

EAC s

## Accessories

### Device marking

US-EMP (20X9) - 0829439



---

### Cable gland with bayonet locking

HC-B-G-M20-PLRBK - 1407669



---

HC-B-G-M25-PLRBK - 1407670



---

HC-B-G-M32-PLRBK - 1407671



## Housing - HC-EVO-B10-CHWS-PLRBK - 1407640

### Accessories

---

HC-B-G-M40-PLRBK - 1407672



### Housing latches

---

HC-B10-SL-PLBK - 1407698



### Corrugated pipe screw connection

---

HC-B-GCA-M20-PLRBK - 1412021



HC-B-GCA-M25-PLRBK - 1411973



HC-B-GCA-M32-PLRBK - 1412022



# Housing - HC-EVO-B10-CHWS-PLRBK - 1407640

## Accessories

HC-B-GCA-M40-PLRBK - 1412023



---

## Seal

HC-B10-SP-RBK - 1407707



---

## Protective cover


HC-B10-BCSFS-P-BK - 1414625



---

## Drawings

### Dimensional drawing



### Dimensional drawing

Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>