

Network cable - VS-M12MSD/5,0-93X/M12MSDOD - 1454244

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Network cable, PROFINET CAT5 (100 Mbps), Ethernet CAT5 (100 Mbps), 4-position, PE-X halogen-free, black-gray RAL 7021, shielded, Plug straight M12 / IP69K, Coding: D, on Plug straight M12 / IP69K, Coding: D, Cable length: 5 m, for outdoor applications, with high-grade steel knurl



Ethernet

Key commercial data

package_quantity	1
GTIN	4046356568852

Technical data

Dimensions

Length of cable	5 m
-----------------	-----

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (operation)	-40 °C ... 85 °C (On sudden changes in temperature (according to IEC 60512-11-4))
Degree of protection	IP65
Degree of protection	IP67
Degree of protection	IP68
Degree of protection	IP69K

General

Rated current at 40°C	4 A
Rated voltage	250 V
Number of positions	4
Coding	D - data
Standards/regulations	M12 connector IEC 61076-2-101
Signal type/category	PROFINET CAT5 (IEC 11801), 100 Mbps
Signal type/category	Ethernet CAT5 (IEC 11801), 100 Mbps
Status display	No
Degree of pollution	3
Insertion/withdrawal cycles	≥ 100
Torque	0.4 Nm (M12 connector)

Material

Network cable - VS-M12MSD/5,0-93X/M12MSDOD - 1454244

Technical data

Material

Flammability rating according to UL 94	V0
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PP
Material of grip body	PP
Material, knurls	Stainless steel
Sealing material	FPM

Standards and Regulations

Standard designation	M12 connector
Standards/regulations	IEC 61076-2-101
Flammability rating according to UL 94	V0

Cable

Cable type	PROFINET outdoors
Cable type (abbreviation)	93X
Cable structure	1x4xAWG22/7; SF/TQ
Conductor cross section	4x 0.34 mm ²
AWG signal line	22
Conductor structure signal line	7x 0.25 mm
Core diameter including insulation	1.95 mm
Wire colors	white-blue, orange-yellow
Overall twist	Star quad
Shielding	Plastic-coated aluminum foil, tinned copper braided shield
Optical shield covering	100 %
External sheath, color	black RAL 9005
Outer sheath thickness	≥ 0.8 mm
External cable diameter D	7.25 mm ±0,3 mm
Minimum bending radius, fixed installation	6 x D
Minimum bending radius, flexible installation	10 x D
Cable weight	81 g/m
Outer sheath, material	PE-X
Material conductor insulation	PE-X
Conductor material	silver-plated Cu litz wires
Conductor resistance	≤ 54.4 Ω/km
Working capacitance	≤ 65 pF (core-core)
Working capacitance	≤ 100 pF (core-shield)
Wave impedance	100 Ω ±5 Ω (f = 100 MHz)
Signal speed	66 c
Shield attenuation	40 dB (30 MHz ≤ f ≤ 100 MHz)
Coupling resistance	200.00 mΩ/m (f ≤ 30 MHz)
Nominal voltage, cable	300 V AC

Network cable - VS-M12MSD/5,0-93X/M12MSDOD - 1454244

Technical data

Cable

Test voltage, cable	2000 V AC (50 Hz, 5 minutes)
Fire protection in rail vehicles	BS 6853 (Category Ia, Ib, II)
Fire protection in rail vehicles	GM/RT 2130 (Category Ia, Ib, II)
Fire protection in rail vehicles	EN 45545 (Risk level HL1 - HL3)
Fire protection in rail vehicles	DIN 5510 (Fire protection level 1, 2, 3, 4)
Fire protection in rail vehicles	NF F16-101 (Category A1, A2, B)
Fire protection in rail vehicles	NF F16-101 (Class C/F0)
Fire protection in rail vehicles	NFPA 130
Fire protection in rail vehicles	UNI CEI 11170 (Risk level LR1 - LR4)
Flame resistance	EN 60332-1-2
Flame resistance	EN 50266
Flame resistance	EN 60332-3-25
Flame resistance	NF C32-070, 2.1
Flame resistance	NF C32-070, 2.2
Flame resistance	UL 1685, 12 (FT4)
Flame resistance	in accordance with ISO 6722-1 5.22 (UN ECE-R 118.01)
Halogen-free	According to EN 50267-2-1
Resistance to oil	according to IRM 902, 72 h at 100 °C
Other resistance	Resistance to fuels according to IRM 903, 168 h at 70 °C
Concentration of fumes	BS 6853 D.8.7
Concentration of fumes	EN 61034-2
Concentration of fumes	UL 1685, 12 (FT4)
Fume corrosiveness	EN 50267-2-2
Fume toxicity	BS 6853 B.1
Fume toxicity	EN 50305, 9.2
Ambient temperature (operation)	-50 °C ... 90 °C (cable, fixed installation)
Ambient temperature (operation)	-40 °C ... 90 °C (cable, flexible installation)

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27060307
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311

ETIM

ETIM 3.0	EC000830
----------	----------

Network cable - VS-M12MSD/5,0-93X/M12MSDOD - 1454244

Classifications

ETIM

ETIM 4.0	EC000830
ETIM 5.0	EC001855

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Accessories

Torque tool

TSD 04 SAC - 1208429



TSD-M 1,2NM - 1212224



Screwdriver tools

TSD-M SAC-BIT ADAPTER - 1212600



Network cable - VS-M12MSD/5,0-93X/M12MSDOD - 1454244


Accessories

SAC BIT M12-W14 - 1212513




Drawings

Dimensional drawing




M12 x 1 plug, straight

Circuit diagram



Contact assignment of the M12 plugs


Schematic diagram



Pin assignment M12 male connector, 4-pos., D-coded, male side

Network cable - VS-M12MSD/5,0-93X/M12MSDOD - 1454244

Cable cross section



PROFINET outdoors [93X]

Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>