



ΔΔΖ

ENERGIZER NH12-800 (HR03)





Typical Discharge Characteristics



Classification: Chemical System: Designation: Nominal Voltage: Rated Capacity:

Typical Weight: Typical Volume: Jacket: Rechargeable Nickel-Metal Hydride (NiMH) ANSI-1.2H1 IEC- HR03 1.2 Volts 800 mAh (to 1.0 volts) Based on 160 mA (0.2C) discharge rate 12 grams (0.42 oz.) 3.8 cubic centimeters Plastic Label

Internal Resistance:

The internal resistance of the cell varies with state of charge, as follows:

Specifications

 Cell Charged
 Cell 1/2 Discharged

 100 milliohms
 120 milliohms

 (tolerance of ±20% applies to above values)
 20%

AC Impedance (No Load):

The impedance of the charged cell varies with frequency, as follows:

Frequency (Hz) 1000 Impedance (milliohms) (Charged Cell) 35

Above values based on AC current set at 1.0 ampere. Value tolerances are $\pm 20\%$.

Operating and Storage Temperatures:

To maintain maximum performance, observe the following general guidelines regarding environmental conditions.

Charge:	0°C to 40°C
Discharge:	0°C to 50°C
Storage:	-20°C to 30°C
Humidity:	65±20%

Operating at extreme temperatures, will significantly impact battery cycle life.

Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication. Contents herein do not constitute a warranty and are for reference only.