



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	David Benfer	Contact Title	Product Compliance Engineer																											
Company Unique ID	485203835	Response Date	2014-04-22	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	5103308-1	Amount	1191.34515	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	111662-1				1.0	1030.0	mg																										
Material	2	PA66-GF25				1.0	1030.0	mg																										
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	41.2	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	61.8	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	36.05	mg																										
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	633.45	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	257.5	mg																										
Sub-Item	1	1888096-8				10.0	16.134515	mg																										
Material	2	Brass				10.0	15.19	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	10.0	0.010633	mg																										
Substance	3	Copper	Supplier	7440-50-8	71.5	10.0	10.86085	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.0	1.519E-4	mg																										
Substance	3	Zinc	Supplier	7440-66-6	27.9975	10.0	4.25282	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.05	10.0	0.007595	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	10.0	1.519E-4	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.05	10.0	0.007595	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.0	0.01519	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	10.0	0.001519	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.0	0.001519	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	10.0	0.001519	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.0	7.595E-5	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.2	10.0	0.03038	mg																										
Material	2	Nickel Plate				10.0	0.52907	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.0	0.00105814	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	10.0	5.2907E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	10.0	0.52748	mg																										

Material	2	Gold Plate				10.0	0.205088	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	10.0	6.1526E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.20447	mg	
Material	2	Tin Plate				10.0	0.184642	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	10.0	1.8446E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	10.0	0.18446	mg	
Material	2	Gold Plate				10.0	0.025715	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.02563786	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	10.0	7.7145E-5	mg	