



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David W Benfer	Contact Title	PROD COMPLIANCE ENGINEER		
Company Unique ID	485203835	Response Date	2014-08-13	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5103309-6	Amount	2506.22938	Version	-	Identity			
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
EUREACH-1213	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1888096-9				26.0	16.30113	mg	
Material	2	Brass Wire				26.0	15.19	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	26.0	0.010633	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	26.0	10.86085	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	26.0	1.519E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	27.9975	26.0	4.25282	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	26.0	0.007595	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	26.0	1.519E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	26.0	0.007595	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	26.0	0.01519	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	26.0	0.001519	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	26.0	0.001519	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	26.0	0.001519	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	26.0	7.595E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	26.0	0.03038	mg	
Material	2	Tin Plate				26.0	0.352	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	26.0	3.5165E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	26.0	0.35165	mg	
Material	2	Gold Plate				26.0	0.00813	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	26.0	2.439E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	26.0	0.00810561	mg	
Material	2	Nickel Plate				26.0	0.607	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	26.0	0.001214	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	26.0	6.07E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	26.0	0.60518	mg	
Material	2	Gold Plate				26.0	0.144	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	26.0	0.14357	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	26.0	4.32E-4	mg	

Sub-Item	1	111662-6				1.0	2082.4	mg	
Material	2	PA66-GF25				1.0	2082.4	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	83.296	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	124.944	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	72.884	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy]	Supplier	32131-17-2	61.5	1.0	1280.676	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	520.6	mg	