



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND																											
Company Unique ID	TE Connectivity	Response Date	2016-04-12	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	5103310-6	Amount	3493.75292038	Version	-	Identity																												
Manufacturer Item Name	A/L LOW PRO HDR 26P RA BLACK	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	BAND ASSY .0245 SQ POST .606 15 AU				13.0	46.83972413	mg																										
Material	2	Nickel Plate				13.0	0.561769	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	0.00112354	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	13.0	5.6177E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	13.0	0.56008	mg																										
Material	2	Brass Wire				13.0	46.0	mg																										
Substance	3	Copper	Supplier	7440-50-8	71.5	13.0	32.89	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	13.0	4.6E-4	mg																										
Substance	3	Zinc	Supplier	7440-66-6	28.0226	13.0	12.8904	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.05	13.0	0.023	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	13.0	4.6E-4	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.05	13.0	0.023	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	13.0	0.046	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	13.0	0.004554	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	13.0	0.0046	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	13.0	0.023	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	13.0	0.0023	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	13.0	2.3E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.2	13.0	0.092	mg																										
Material	2	Gold Plate				13.0	0.0252934	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.02521752	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	7.58802E-5	mg																										
Material	2	Tin Plate				13.0	0.246189	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	4.9238E-4	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.73	13.0	0.24552	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	13.0	1.7233E-4	mg																										

Material	2	Gold Plate				13.0	0.00647273	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	1.941819E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.00645331	mg	
Sub-Item	1	BAND ASSY .0245 SQ POST .805 15 AU				13.0	61.72588513	mg	
Material	2	Nickel Plate				13.0	0.74793	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	0.00149586	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	13.0	7.4793E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	13.0	0.74569	mg	
Material	2	Brass Wire				13.0	60.7	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	13.0	43.4005	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	13.0	6.07E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	13.0	17.00972	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	13.0	0.03035	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	13.0	6.07E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	13.0	0.03035	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	13.0	0.0607	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	13.0	0.0060093	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	13.0	0.00607	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	13.0	0.03035	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	13.0	0.003035	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	13.0	3.035E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	13.0	0.1214	mg	
Material	2	Gold Plate				13.0	0.0252934	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.02521752	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	7.58802E-5	mg	
Material	2	Tin Plate				13.0	0.246189	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	4.9238E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	13.0	0.24552	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	13.0	1.7233E-4	mg	
Material	2	Gold Plate				13.0	0.00647273	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	1.941819E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.00645331	mg	
Sub-Item	1	026 HOUSING LOPRO HDR				1.0	2082.4	mg	
Material	2	PA66-GF25				1.0	2082.4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	72.884	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	83.296	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	520.6	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	1280.676	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	124.944	mg	