


PRODUCT NUMBER
73305-XXXLF

PLATING OPTION	
1=	GXT 0.76 μm
3=	GOLD 0.76 μm
5=	GOLD 1.27 μm

PACKAGE OPTION	
1=	TAPE ON REEL
2=	TUBE
3=	TAPE ON REEL IN PLASTIC BAG

TERMINAL LOADING	
1=	FULLY LOADED
2=	POS 2,3,4,5
3=	POS 1,2,5,6

WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 4.




REFERENCE PLAN
DEFINED BY THE
2 HOLD DOWN
BEARING SURFACE

NOTES:

- 1 - MATERIAL: HOUSING: HIGH TEMP. PCT, COLOUR BLACK.
TERMINAL: PHOSPHOR BRONZE.
- 2 - PLATING: CONTACT AREA: SEE TABLE.
SOLDER TAIL : 90/10 SnPb 2 μm MIN.
WHEN SUFFIX "LF" IS REQUIRED, 2 μm MIN MATTE
TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.
NO RAW EDGES EXCEPT SOLDER TAIL TIPS
- 3 - SOLDER TAILS COPLANARITY : 0.1 mm
- 4 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2 μm MINIMUM MATTE TIN OVER 1.27 μm
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO
245°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004
- 5 - PACKAGING FOR OPTION 3 : EACH REEL IS WRAPPED INTO A PLASTIC BAG
TO PROTECT FROM MOISTURE DURING STACKING TIME.

VIEW ACCORDING "V"






SEE NOTE 3

CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface ISO 1302 <input checked="" type="checkbox"/> ISO 406 ISO 1101		tolerance ISO 406 ISO 1101		projection 		product family MOD JACK	
ltr ecn no dr date				tolerances unless otherwise specified		±0.13		mm		title SMT RA JACK 6 POS OUTSIDE	
H F06-024D DLE 06.07.18				angles		linear		scale 2:1		dwg no 73305	
J F09-007D LSA 09.07.23				±2'						sheet 1 of 3 size A3	
K B-15798 JFA 13.09.09										type CUSTOMER Drawing	
L F-21888 AMA 15.09.09				dr		D LEGRAND 04.10.18					
				enrg		P NIZZI 04.10.18					
F F04-0363 DLE 04.10.18				chr		D LEGRAND 04.10.18					
G F05-0247 DLE 05.09.12				app		P.NZ 04.10.18					
sheet index		revision		L		E		B			
sheet		1		2		3					



PRODUCT NUMBER
SEE SHEET 1

LTR	PART NAME	QTY
1	PRODUCT	230
2	TAPE	1
3	REEL	1
4	COVER TAPE	1




1- IN ACCORDANCE WITH EIA-481 AND IEC 296-3

CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code		surface ISO 1302 <input checked="" type="checkbox"/> tolerance ISO 406 ISO 1101		projection 		product family MOD-JACK	
ltr ecn no dr date		tolerances unless otherwise specified		mm 		title SMT RA JACK 6 POS. OUTSIDE	
D	F80620	DLE	98.11.26	angles linear	scale 1:1		dwg no 73305 sheet 2 of 3 size A3
E	F06-024Q	DLE	06.07.18	dr D LEGRAND 06.07.18	engr P NIZZI 06.07.18		chr D LE 06.07.18
sheet index		revision sheet		app P NZ 06.07.18		type CUSTOMER Drawing	





A

A

B

B

C

C

D

D



FCIconnect.com

CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code		surface	tolerance	projection	product family	
		ISO 1302 <input checked="" type="checkbox"/>	ISO 406 ISO 1101		MOD JACK	
ltr	ecn no	dr	date	title		
A	F04-0363	DLE	04.10.18	SMT RA JACK 6 POS OUTSIDE		
B	F06-0240	DLE	06.07.18			
		angles	linear	mm		
		±2'	±0.13	← mm →		
				scale 2:1		
		dr	D LEGRAND	04.10.18	dwg no	
		engr	P NIZZI	04.10.18	sheet 3 of - size	
		chr	D LEGRAND	04.10.18	73305 A4	
		appd	P NZ	04.10.18	type	
				CUSTOMER Drawing		
sheet index	revision sheet					



Copyright FCI