



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer, David W	<b>Contact Title</b>	Prod Compliance Engineer for DND		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2015-07-10	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1-5103308-0	<b>Amount</b>	4041.22575	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	A/L LOW PRO HDR 50P VERT BLACK	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1214</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	050 HOUSING LOPRO HDR				1.0	3234.5	mg	
Material	2	PA66-GF25				1.0	3234.5	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	113.2075	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	129.38	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	808.625	mg	
Substance	3	Poly[[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]]	Supplier	32131-17-2	61.5	1.0	1989.2175	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	194.07	mg	
Sub-Item	1	BAND ASSY .0245 SQ POST .493 15 AU				50.0	16.134515	mg	
Material	2	Gold Plate				50.0	0.205088	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	50.0	6.1526E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	0.20447	mg	
Material	2	Nickel Plate				50.0	0.52907	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	50.0	0.00105814	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	50.0	5.2907E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	50.0	0.52748	mg	
Material	2	Brass Wire				50.0	15.19	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	50.0	10.86085	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	50.0	1.519E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	27.9975	50.0	4.25282	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	50.0	0.007595	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	50.0	1.519E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	50.0	0.007595	mg	

Substance	3	Cobalt	Supplier	7440-48-4	0.1	50.0	0.01519	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	50.0	0.001519	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	50.0	0.001519	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	50.0	0.010633	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	50.0	0.001519	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	50.0	7.595E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	50.0	0.03038	mg	
Material	2	Gold Plate				50.0	0.025715	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	0.02563786	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	50.0	7.7145E-5	mg	
Material	2	Tin Plate				50.0	0.184642	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	50.0	1.8446E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	50.0	0.18446	mg	