



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	DAVID BENFER	Contact Title	Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2015-10-09	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	5103308-3	Amount	1.52845224	Version	-	Identity																												
Manufacturer Item Name	A/L LOW PRO HDR 16P VERT BLACK	Weight Uom	g	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	016 HOUSING LOPRO HDR				1.0	1.2703	g																										
Material	2	PA66-GF25				1.0	1.2703	g																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	0.0444605	g																										
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	0.050812	g																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	0.317575	g																										
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	0.7812345	g																										
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	0.076218	g																										
Sub-Item	1	BAND ASSY .0245 SQ POST .493 15 AU				16.0	0.01613451	g																										
Material	2	Gold Plate				16.0	2.0509E-4	g																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	16.0	6.15264E-7	g																										
Substance	3	Gold	Supplier	7440-57-5	99.7	16.0	2.0447E-4	g																										
Material	2	Nickel Plate				16.0	5.2907E-4	g																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	16.0	1.05814E-6	g																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	16.0	5.2907E-7	g																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	16.0	5.2748E-4	g																										
Material	2	Tin Plate				16.0	1.8464E-4	g																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	16.0	1.844574E-7	g																										
Substance	3	Tin	Supplier	7440-31-5	99.9001	16.0	1.8446E-4	g																										
Material	2	Gold Plate				16.0	2.5715E-5	g																										
Substance	3	Gold	Supplier	7440-57-5	99.7	16.0	2.563786E-5	g																										

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	16.0	7.7145E-8	g	
Material	2	Brass Wire				16.0	0.01519	g	
Substance	3	Copper	Supplier	7440-50-8	71.5	16.0	0.01086085	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	16.0	1.519E-7	g	
Substance	3	Zinc	Supplier	7440-66-6	27.9975	16.0	0.00425282	g	
Substance	3	Manganese	Supplier	7439-96-5	0.05	16.0	7.595E-6	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	16.0	1.519E-7	g	
Substance	3	Iron	Supplier	7439-89-6	0.05	16.0	7.595E-6	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	16.0	1.519E-5	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	16.0	1.519E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	16.0	1.519E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	16.0	1.0633E-5	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	16.0	1.519E-6	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	16.0	7.595E-8	g	
Substance	3	Nickel	Nickel	7440-02-0	0.2	16.0	3.038E-5	g	