



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer																											
Company Unique ID	485203835	Response Date	2013-12-05	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	5103310-8	Amount	4807.5821852	Version	-	Identity																												
Manufacturer Item Name		Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions - true																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	1-1888096-8				20.0	61.72588513	mg																										
Material	2	Brass				20.0	60.7	mg																										
Substance	3	Copper	Supplier	7440-50-8	71.5	20.0	43.4005	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	20.0	6.07E-4	mg																										
Substance	3	Zinc	Supplier	7440-66-6	27.9975	20.0	16.99448	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.05	20.0	0.03035	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	20.0	6.07E-4	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.05	20.0	0.03035	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	20.0	0.0607	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	20.0	0.00607	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	20.0	0.00607	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	20.0	0.04249	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	20.0	0.00607	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	20.0	3.035E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.2	20.0	0.1214	mg																										
Material	2	Nickel Plate				20.0	0.74793	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	20.0	0.00149586	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	20.0	7.4793E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	20.0	0.74569	mg																										
Material	2	Gold Plate				20.0	0.00647273	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	20.0	0.00645331	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	20.0	1.941819E-5	mg																										
Material	2	Tin Plate				20.0	0.246189	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	20.0	2.4594E-4	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.9001	20.0	0.24594	mg																										
Material	2	Gold Plate				20.0	0.0252934	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	20.0	0.02521752	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	20.0	7.58802E-5	mg																										
Sub-Item	1	1-1888096-4				20.0	46.83972413	mg																										
Material	2	Brass				20.0	46.0	mg																										

Substance	3	Copper	Supplier	7440-50-8	71.5	20.0	32.89	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	20.0	4.6E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	27.9975	20.0	12.87885	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	20.0	0.023	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	20.0	4.6E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	20.0	0.023	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	20.0	0.046	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	20.0	0.0046	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	20.0	0.0046	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	20.0	0.0322	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	20.0	0.0046	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	20.0	2.3E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	20.0	0.092	mg	
Material	2	Nickel Plate				20.0	0.561769	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	20.0	0.00112354	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	20.0	5.6177E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	20.0	0.56008	mg	
Material	2	Gold Plate				20.0	0.00647273	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	20.0	0.00645331	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	20.0	1.941819E-5	mg	
Material	2	Tin Plate				20.0	0.246189	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	20.0	2.4594E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	20.0	0.24594	mg	
Material	2	Gold Plate				20.0	0.0252934	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	20.0	0.02521752	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	20.0	7.58802E-5	mg	
Sub-Item	1	111662-8				1.0	2636.27	mg	
Material	2	PA66-GF25				1.0	2636.27	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	105.4508	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	158.1762	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	92.26945	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	1621.30605	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	659.0675	mg	