

VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“For more than 25 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

LIPO 4000 CHARGER V-CHARGE ECO

CE
VERSION 02/16

Nº 1406443

User-friendly LiPo charger for a rechargeable battery pack with up to 4 LiPo cells. Simply plug the rechargeable battery in and charging process will start.

FEATURES:


For 2 - 4 LiPo cells // 4,000 mA charging current //

EQUIPMENT:

4 LEDs to indicate the charge status // Integrated supply unit // Over temperature protection // Temperature-controlled device fans // Balancer cells voltage adaptation //

TECHNICAL DATA:

Number of charging channels	1
Suitable rechargeable battery	LiPo
Appropriate for	2 - 4 cells
Capacity range of charging battery	1800 - 10000 mAh
Cell voltage	3.7 V
Charging current (max.)	4,000 mA
Charging capacity max	50 W
Charging indicator	4 LEDs, 25/50/75/100%
Charging shutdown/cell	4.24 V
Balancer plug-in system	XH
Balancer current	300 mA
Operating voltage	100 - 240 V/AC
Protection class	2
Ambient conditions	+10 °C to +40 °C, from 0 to 90% relative humidity, non-condensing
Product dimensions (L x W x H)	98 x 98 x 36 mm
Weight	278 g



PACKAGE CONTENTS:

Charger // Power cable // Operating instructions //

Legal notice

This data sheet is published by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data sheet represent the technical status at the time of printing.

© Copyright 2016 by Conrad Electronic SE

V1_0216_02/VTP