



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	David W Benfer	<b>Contact Title</b>	PROD COMPLIANCE ENGINEER		
<b>Company Unique ID</b>	485203835	<b>Response Date</b>	2014-04-14	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1-5499786-0	<b>Amount</b>	11513.29473	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions - true								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	5-102132-7				25.0	52.0541886	mg	
Material	2	Nickel Plate				25.0	0.919855	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	25.0	0.00183971	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	25.0	9.1986E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	25.0	0.9171	mg	
Material	2	Gold Plate				25.0	0.0473176	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	25.0	0.04717565	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	25.0	1.4195E-4	mg	
Material	2	Gold Plate				25.0	0.043016	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	25.0	0.04288695	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	25.0	1.2905E-4	mg	
Material	2	Brass				25.0	50.891	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	25.0	0.050891	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	25.0	32.57024	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	25.0	0.0254455	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	25.0	0.0050891	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	25.0	5.0891E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	25.0	0.050891	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	25.0	0.050891	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	25.0	17.91796	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	25.0	0.0050891	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	25.0	0.0050891	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	25.0	0.0254455	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	25.0	0.15267	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	25.0	2.5446E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	25.0	0.0050891	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	25.0	0.0254455	mg	
Material	2	Tin Plate				25.0	0.153	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	25.0	1.5285E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	25.0	0.15285	mg	

Sub-Item	1	102142-5				1.0	7610.0	mg	
Material	2	PBT-GF30FR(17)				1.0	7610.0	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	1.0	2283.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	1.0	2511.3	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	76.1	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	76.1	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	380.5	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	2283.0	mg	
Sub-Item	1	102320-1				2.0	449.0	mg	
Material	2	PBT-GF30FR(17)				2.0	449.0	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	2.0	134.7	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	2.0	148.17	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	2.0	4.49	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	2.0	4.49	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	2.0	22.45	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	2.0	134.7	mg	
Sub-Item	1	5-102132-9				25.0	68.1576006	mg	
Material	2	Nickel Plate				25.0	1.124267	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.2	25.0	0.00224853	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	25.0	0.00112427	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	25.0	1.12089	mg	
Material	2	Gold Plate				25.0	0.0473176	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	25.0	0.04717565	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	25.0	1.4195E-4	mg	
Material	2	Gold Plate				25.0	0.043016	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	25.0	0.04288695	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	25.0	1.2905E-4	mg	
Material	2	Brass				25.0	66.79	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	25.0	0.06679	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	25.0	42.7456	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	25.0	0.033395	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	25.0	0.006679	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	25.0	6.679E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	25.0	0.06679	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	25.0	0.06679	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	25.0	23.51576	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	25.0	0.006679	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	25.0	0.006679	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	25.0	0.033395	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	25.0	0.20037	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	25.0	3.3395E-4	mg	

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	25.0	0.006679	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	25.0	0.033395	mg	
Material	2	Tin Plate				25.0	0.153	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	25.0	1.5285E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	25.0	0.15285	mg	