

DATASHEET

XLR connector, female, 3 pin

Version 11/15

Item no. 1409085/1409086/1409087



Color.....	Blue/yellow//red
No. of pins.....	3
Audio Channel.....	stereo
Contact plated.....	Nickel
Connection.....	Soldering
Category.....	XLR female
Connector type.....	Jack,straight
Mating cycles.....	> 3000
Dimension.....	71.75*21.2*20.4 mm
Tolerance.....	±1 mm
Housing material&coating.....	zinc alloy/nickel plating
Contact resistance.....	≤ 3 mΩ
Mechanical life(cycles).....	>1000 cycles
Insertion and withdrawal force.....	≤ 20 N
Cable diameter can be used.....	3.5-8.0 mm
Dielectric strength.....	1.4 kV dc
Operation voltage.....	50 V ac

Operation temperature and humidity.....	-25 degree Celsius to +80 degree Celsius / 10%-90%
Storage temperature and humidity.....	-25 degree Celsius to +80 degree Celsius / 10%-90%



This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2013 by Conrad Electronic SE.