



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Kim, Seong Kyung	Contact Title	Account Manager		
Company Unique ID	TE Connectivity	Response Date	2015-03-26	Contact Email	sophie.kim@te.com				
Contact Phone Number	82-2-3415-4614								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-1658526-3	Amount	3343.82	Version	-	Identity			
Manufacturer Item Name	609-2041LF FEM SOCKET, LEAD FREE	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	D1561-20=CAP, CON NECTOR, WRA P PO				1.0	159.9	mg	
Material	2	PBT-GF30-FR(17)				1.0	159.9	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	51.0	1.0	81.549	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	8.0	1.0	12.792	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.0	1.0	46.371	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	6.396	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	8.0	1.0	12.792	mg	
Sub-Item	1	D4640-20=STRAIN RELIEF, H/D WW				1.0	758.17	mg	
Material	2	PBT-GF30-FR(17)				1.0	758.17	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	51.0	1.0	386.6667	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	8.0	1.0	60.6536	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.0	1.0	219.8693	mg	

Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	30.3268	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	8.0	1.0	60.6536	mg	
Sub-Item	1	T&B D3179-12 CONTACT, LEAD FREE				20.0	36.017	mg	
Material	2	Gold Plate				20.0	0.0040	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	20.0	0.003988	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	20.0	1.2E-5	mg	
Material	2	Nickel Plate				20.0	0.621	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	20.0	0.001242	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	20.0	6.21E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	20.0	0.61914	mg	
Material	2	Beryllium Copper				20.0	35.338	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	20.0	0.0035338	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.6	20.0	0.21203	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	20.0	3.5338E-4	mg	
Substance	3	Beryllium	Supplier	7440-41-7	2.0	20.0	0.70676	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	20.0	0.0070676	mg	
Substance	3	Iron	Supplier	7439-89-6	0.6	20.0	0.21203	mg	
Substance	3	Copper	Supplier	7440-50-8	96.0485	20.0	33.94162	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	20.0	0.0035338	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.6	20.0	0.21203	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	20.0	0.0035338	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	20.0	1.7669E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	20.0	0.035338	mg	
Material	2	Tin Plate				20.0	0.054	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	20.0	5.3946E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	20.0	0.05394605	mg	
Sub-Item	1	D1222-20A=BASE POL 20 POS W/W				1.0	1202.13	mg	
Material	2	PBT-GF30-FR(17)				1.0	1202.13	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	51.0	1.0	613.0863	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	8.0	1.0	96.1704	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.0	1.0	348.6177	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	48.0852	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	8.0	1.0	96.1704	mg	
Sub-Item	1	D1109-20=COVER 20 POS W/W				1.0	503.28	mg	

Material	2	PBT-GF30-FR(17)				1.0	503.28	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	51.0	1.0	256.6728	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	8.0	1.0	40.2624	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.0	1.0	145.9512	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	20.1312	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	8.0	1.0	40.2624	mg	