





TOOLCRAFT

GB Data sheet

Quiet packaging tape

Item no. 1417380



Technical data

- Length..... 50 m
- Width 48 mm
- Thickness 50 micron
- Material..... BOPP (biaxially oriented polypropylene)
- Colour..... brown
- Operating temperature -20 to +60 °C
- Operating humidity 10 – 90 % RH
- Storage temperature..... -10 to +50 °C
- Storage humidity..... 5 – 90 % RH

Performance index

Item	Units	Performance	Test mode
180° peel strength	N/25 mm	≥6.5	GB/T 2792-1998
180° to backing	N/25 mm	≤2.8	GB/T 4850-2002
Holding power	mm/h·23 °C·25 mm x 25 mm	≤0.3	GB/T 4851-1998
Initial tack	#	≥13	GB/T 4852-2002
Substrate	/	BOPP	/
Seclusion paper	g/m ²	/	/
Substrate thickness	mm	0.028±0.002	GB/T 7125-1999
Adhesion thickness	mm	0.050±0.002	GB/T 7125-1999
Adhesives	/	Acrylic	/
Colour	/	Brown	/
Tensile strength	N/10 mm	≥30	GB/T 7753-1987
Breakpoint elongation	%	≤180	GB/T 7753-1987
Heat resistance	°C	/	/
Storage life	Year	1	GB/T 7123.2-2002
Solvent resistance	Min	30	GB/T 13353-1992
Resistance flammability	/	/	GB/T 15903-1995
Weathers	/	Excellent	/
Remark	Packing, bundling, etc.		

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.

Copyright 2016 by Conrad Electronic SE.

*1417380_V1_0616_02_IPL_ds