



TOOLCRAFT

® Data sheet

Automotive foam tape

Item no. 1417386

Technical data

Length..... 30 m
 Width 20 mm
 Thickness 0.8 mm
 Colour red
 Operating temperature -10 to +50 °C
 Operating humidity 10 – 90 % RH
 Storage temperature..... -10 to +50 °C
 Storage humidity..... 5 – 90 % RH

Performance index

Item	Units	Performance	Test mode
180° peel strength	N/25 mm	≥20	GB/T 2792-1998
180° to backing	N/25 mm	/	GB/T 4850-2002
Holding power	h/23 °C·kg·25 mm x 25 mm	≥48	GB/T 4851-1998
Tack	#	15	GB/T 4852-2002
Substrate	/	IXPE	/
Seclusion paper	g/m ²	60±5 red liner paper	/
Adhesion thickness	mm	0.8	GB/T 7125-1999
Adhesives	/	Acrylic	/
Colour	/	Red/Black	/
Tensile strength	N/10 mm	≥7.5	GB/T 7753-1987
Breakpoint elongation	%	≥230	GB/T 7753-1987
Heat resistance	°C	-10~100	/
Storage life	Year	1	GB/T 7123.2-2002
Solvent resistance	Min	/	GB/T 13353-1992
Resistance flammability	/	/	GB/T 15903-1995
Weathers	/	Good	/

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.

Copyright 2016 by Conrad Electronic SE.

*1417386_V1_0616_02_IPL_ds