

## Products » LED warning lights » FT-100 LED

Range of modern and energy-efficient **FT-100 LED** warning beacons (**available both with a single and a double flash**) made of high quality components that make the lamps long lasting and maintenance free.

[Film with FT-100 LED lamp.](#)

Available: 6 product versions:

- FT-100 3S LED :- LED warning beacon, single flash, yellow, mounted on 3 screws with a 1,5m cable
- FT-100 3S DF LED :- LED warning beacon, double flash, yellow, mounted on 3 screws with a 1,5m cable
- FT-100 LED MAG M30 :- portable LED warning beacon, single flash, yellow, mounted on a magnet pad, equipped with a spiral cable (unfolded - 3m, in spiral - 0,6m) and a standard 12/ 24V lighter plug
- FT-100 DF LED MAG M30 :- portable LED warning beacon, double flash, yellow, mounted on a magnet pad, equipped with a spiral cable (unfolded - 3m, in spiral - 0,6m) and a standard 12/ 24V lighter plug
- FT-100 LED MAG M78 :- portable LED warning beacon, single flash, yellow, mounted on a magnet pad, equipped with a spiral cable (unfolded - 7.8m, in spiral - 1,2m) and a standard 12/ 24V lighter plug
- FT-100 DF LED MAG M78 :- portable LED warning beacon, double flash, yellow, mounted on a magnet pad, equipped with a spiral cable (unfolded - 7.8m, in spiral - 1,2m) and a standard 12/ 24V lighter plug



### Technical specification:

- application of 20 CREE LED diodes
- universal supply voltage **12-55V**

**Peak power consumption: 2A/1A/0,5A, average power consumption: 0,8A/0,4A/0,2A**

Peak/average rated power: **25W/10W**

- special warning lamp approval compliant with **ECE Regulation 65 (TA1)**

- flash frequency: **f = 2,0 Hz**

- ElectroMagnetic Compatibility - **EMC certificate**

- full waterproofness (**IP68**)




- shock-resistance - **IK**

- operating temperature: **- 40°C to + 55°C**

- reverse polarity protection system

- fixed polarisation: **GROUND** - white wire; (+) - black wire

ID/EAN	Photo	Description	Individual package		Carton			Palette		
			qty.	kg	qty.	cm	kg	qty.	cm	kg
FT-100 3S LED		Yellow LED warning beacon, mounted on 3 screws. Cable's length 1.5 m.	1	0,70	18	59x39x29	12,60	360	120x80x165	277,00
FT-100 LED MAG M30		Yellow LED warning beacon mounted on a magnet. Additionally, the lamp is equipped with a spiral cable (unfolded - 3 m, in spiral - 0,6 m) and a standard 12/ 24V lighter plug.	1	1,35	18	59x39x29	24,30	360	120x80x165	511,00
FT-100 LED MAG M78		Yellow LED warning beacon mounted on a magnet. Additionally, the lamp is equipped with a spiral cable (unfolded - 7.8 m, in spiral - 1.2 m) and a standard 12/ 24V lighter plug.	1	1,55	18	59x39x29	27,90	360	120x80x165	583,00
FT-100 3S DF LED		Yellow LED warning beacon, double flash, mounted on 3 screws, cable's length 1.5 m.	1	0,70	18	59x39x29	12,60	360	120x80x165	277,00
FT-100 DF LED MAG M30		Yellow LED warning beacon, double flash, portable version mounted on a magnet pad. The lamp is equipped with a spiral cable (unfolded - 3 m, in spiral - 0.6 m) and a standard 12/ 24V lighter plug.	1	1,35	18	59x39x29	24,30	360	120x80x165	511,00
FT-100 DF LED MAG M78		Yellow LED warning beacon, double flash, portable version mounted on a magnet pad. The lamp is equipped with a spiral cable (unfolded - 7.8 m, in spiral - 1.2 m) and a standard 12/ 24V lighter plug.	1	1,55	18	59x39x29	27,90	360	120x80x165	583,00

										
FT-100 LED PI		Yellow LED warning beacon, single flash. The lamp appears in a stationary version with a pipe-socket.	1	1,35	10	59x39x29	13,50	200	120x80x165	295,00
FT-100 DF LED PI		Yellow LED warning beacon, double flash. The lamp appears in a stationary version with a pipe-socket.	1	1,35	10	59x39x29	13,50	200	120x80x165	295,00