


Dimensions of Bare Cell		H	33.0 ±0.3 mm
			1.299 ±0.012 inch
		D	22.0 ±0.3 mm
			0.866 ±0.012 inch
		d	10.0 mm
			0.394 inch


Nominal Capacity		1200mAh	
Nominal Voltage		1.2V	
Charging Current	Standard	125mA	
	Quick	375mA	
	Fast	1900mA	
Charging Time	Standard	14 to 16Hrs.	
	Quick	4 to 6Hrs.	
	Fast	about 1Hr.	
Ambient Temperature	Charge	Standard	0°C to +45°C [+32°F to 113°F]
		Quick	10°C to +45°C [+50°F to 113°F]
		Fast	5°C to +40°C [+41°F to 104°F]
	Discharge	-20°C to +60°C [-4°F to 140°F]	
	Storage	-30°C to +50°C [-22°F to 122°F]	
Internal Impedance (Av.) (at 50% discharge)		5.0mΩ (at 1000Hz)	
Weight		43g/1.52oz	
Dimensions(D)×(H) (with tube)		22.9 <sup>0</sup> <sub>-1</sub> × 34.0 <sup>0</sup> <sub>-1.2</sub> mm	
		0.90 <sup>0</sup> <sub>-0.04</sub> × 1.34 <sup>0</sup> <sub>-0.05</sub> inch	

### Typical Characteristics


Charge Characteristics (5 cells pack)




Discharge (at high rate)




Cell Capacity (at various discharge rate)



Discharge (at high rate)



Discharge (at low rate)



Temperature (Charge & Discharge)

