

Miniature circuit breaker 230/400 V 10kA, 1-pole, D, 0.5A



Model	
Product brand name	SENTRON
Product designation	Miniature circuit breaker
Design of the product	5SL miniature circuit breakers
General technical data	
Number of poles	1
Number of poles / Note	1P
Tripping characteristic class	D
circuit-breaker / Design	5SL4
Mechanical service life (switching cycles) / typical	10 000
Overvoltage category	3
Voltage	
Insulation voltage	
<ul style="list-style-type: none"> with single-phase operation / at AC / rated value 	250 V
<ul style="list-style-type: none"> with multi-phase operation / at AC / rated value 	440 V
Supply voltage	
Type of voltage	AC

Current / at AC / rated value	0.5 A
Supply voltage / at AC / rated value	400 V
Operating voltage	
• with multi-phase operation / at AC / maximum	440 V
• at DC / rated value / maximum	60 V
Supply voltage frequency	
• rated value	50 Hz

Protection class	
Protection class IP	IP20, with connected conductors

Switching capacity	
Switching capacity current	
• acc. to EN 60898 / rated value	10 kA
• acc. to IEC 60947-2 / rated value	10 kA
Energy limiting class	3

Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	0.9 W

Current	
Tripping residual / rated value / derated current / at 40 Cel	0.47 A
Suitability for operation	Residential buildings/infrastructure

Product details	
Product function / neutral conductor switching	No
Product feature / Touch protection	Yes
Product feature	
• halogen-free	Yes
• sealable	Yes
• silicon-free	Yes
Product extension / can be installed / supplementary devices	Yes

Connections	
• Connectable conductor cross-section	
— solid	0.75 ... 25 mm ²
— stranded	0.75 ... 25 mm ²
• Connectable conductor cross-section / finely stranded / with core end processing	0.75 ... 25 mm ²
Tightening torque / with screw-type terminals	2.5 ... 3 N·m

Mechanical Design	
Height	90 mm
Width	18 mm

Depth	76 mm
Installation depth	70 mm
Number of width units	1
Mounting position	any
Net weight	145 g

Environmental conditions

Influence of the surrounding temperature	+55 °C, max. 95% humidity
Ambient temperature	-25 ... +55 °C
• during storage	-40 ... +75 °C

Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

General Product Approval

Test Certificates



[Miscellaneous](#)

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SL4105-8>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SL4105-8>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SL4105-8

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



